

ST0569




Flow monitor

SCE18ADBFPKG/US-100-IPF

Article no longer available - archive entry

Alternative articles: SI5010 + E40104

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	T-piece QL 18 / ST DIN 2353

Application

Application	high pressure
Media	Liquids
Medium temperature [°C]	10...50
Pressure rating [bar]	300

Electrical data

Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20

Inputs / outputs


Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

ST0569



Flow monitor

SCE18ADBFPKG/US-100-IPF

Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Setting range	[cm/s]	100...500
Accuracy / deviations		
Temperature gradient	[K/min]	300
Response times		
Response time	[s]	1...2
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	10...60
Protection		IP 67
Mechanical data		
Dimensions	[mm]	60 x 41 x 101
Materials		PBT-GF20
Materials (wetted parts)		stainless steel (1.4571/316Ti)
Process connection		T-piece QL 18 / ST DIN 2353
Displays / operating elements		
Display	function	11 x LED
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12		
		

ST0569



Flow monitor

SCE18ADBFPKG/US-100-IPF

Connection

