


# SA6014



## Flow sensor

SAN12XDB50KG/US-100



| Product characteristics                      |  |
|--|--|
| Number of inputs and outputs                 | Number of analogue outputs: 2  |
| Process connection                           | threaded connection 1/2" NPT external thread   |
| Application                                  |  |
| Special feature                              | Gold-plated contacts   |
| Media  | water; glycol solutions; air; oils   |
| Note on media                                | low-viscosity oils with viscosity: $\leq 40 \text{ mm}^2/\text{s}$ (104 °F)<br>high-viscosity oils with viscosity: $> 40 \text{ mm}^2/\text{s}$ (104 °F) |
| Medium temperature [°F]                      | -4...194   |
| Pressure rating                              | 100 bar   1450 psi   10 MPa  |
| MAWP for applications according to CRN [bar] | 100  |
| Electrical data                              |  |
| Operating voltage [V]                        | 18...30 DC   |
| Current consumption [mA]                     | < 100  |
| Protection class                             | III  |
| Reverse polarity protection                  | yes  |
| Power-on delay time [s]                      | 10   |
| Measuring principle                          | calorimetric   |



## Flow sensor

SAN12XDB50KG/US-100

| Inputs / outputs                       |   |
|--|---|
| Number of inputs and outputs           | Number of analogue outputs: 2   |
| Outputs                                |   |
| Total number of outputs                | 2   |
| Output signal                          | analogue signal   |
| Number of analogue outputs             | 2   |
| Analogue current output [mA]           | 4...20; (scalable)  |
| Max. load [ $\Omega$ ]                 | 350   |
| Short-circuit protection               | yes   |
| Type of short-circuit protection       | pulsed  |
| Overload protection                    | yes   |
| Measuring/setting range                |   |
| Probe length L [mm]                    | 26.6  |
| Operating mode                         | relative; absolutely liquid; absolutely gaseous; (absolute: reference measurement recommended; Factory setting: relative) |
| Liquids                                |   |
| Resolution [ft/s]                      | 0.05  |
| Analogue start point ASP [ft/s]        | 0...7.95  |
| Analogue end point AEP [ft/s]          | 1.9...9.85  |
| Gases                                  |   |
| Resolution [ft/s]                      | 2   |
| Analogue start point ASP [ft/s]        | 0...264   |
| Analogue end point AEP [ft/s]          | 64...328  |
| Temperature monitoring                 |   |
| Measuring range [ $^{\circ}$ F]        | -4...194  |
| Resolution [ $^{\circ}$ F]             | 0.5   |
| Analogue start point [ $^{\circ}$ F]   | -4...169  |
| Analogue end point [ $^{\circ}$ F]     | 39...212  |
| In steps of [ $^{\circ}$ F]            | 0.5   |
| Liquid media - absolute operating mode |   |
| Setting range [ft/s]                   | 0...9.85  |
| Greatest sensitivity [ft/s]            | 0.15...9.85   |
| Liquid media - relative operating mode |   |
| Setting range [ft/s]                   | 0...19.5  |
| Greatest sensitivity [ft/s]            | 0.15...9.85   |
| Gases - operating mode "absolute"      |   |
| Setting range [ft/s]                   | 6...328   |
| Greatest sensitivity [ft/s]            | 6...328   |
| Gases - operating mode "relative"      |   |
| Setting range [ft/s]                   | 6...656   |
| Greatest sensitivity [ft/s]            | 6...328   |

# SA6014



## Flow sensor

SAN12XDB50KG/US-100

| Accuracy / deviations         |                 |  |
|-------------------------------|-----------------|--|
| Temperature drift             | [cm/s x 1/K]    | 0,01 fps x 1/K (< 68 °F; > 158 °F)   |
| Temperature gradient          | [K/min]         | 100  |
| Absolute operating mode       |                 |  |
| Repeatability                 |                 | 0,05 m/s; (water; flow velocity: 0,05...3 m/s)   |
| Relative operating mode       |                 |  |
| Accuracy                      |                 | ± (7 % MW + 2 % MEW); (for relative mode in the range of maximum sensitivity under the following conditions:; water: 68...158 °F; inlet length: 5 ft; DN25 (DIN 2448); mounting position according to instructions; Accuracy can differ for other media and mounting positions.) |
| Repeatability                 |                 | 0,05 m/s; (water; flow velocity: 0,05...3 m/s)   |
| Temperature monitoring        |                 |  |
| Temperature drift             |                 | ± 0,003 K/°F   |
| Accuracy                      | [K]             | ± 0,3 / ± 1; (water; flow velocity: 1...9,85 fps / air; flow velocity: > 32,8 fps)   |
| Response times                |                 |  |
| Response time                 | [s]             | 0.5; (T09; water; glycol: 0,8 s; air: 7 s; oil: 1,8 s; each T09)   |
| Temperature monitoring        |                 |  |
| Dynamic response T05 / T09    | [s]             | 1,5 (T09); (water; flow velocity: 1...9,85 fps)  |
| Software / programming        |                 |  |
| Parameter setting options     |                 | medium selection; Damping; Teach function; display can be rotated and switched off; standard unit of measurement; process value colour   |
| Operating conditions          |                 |  |
| Ambient temperature           | [°F]            | -40...176  |
| Storage temperature           | [°F]            | -40...212  |
| Protection                    |                 | IP 65; IP 67   |
| Tests / approvals             |                 |  |
| EMC                           |                 | DIN EN 60947-5-9   |
| Shock resistance              |                 | DIN EN 60068-2-27 50 g (11 ms)   |
| Vibration resistance          |                 | DIN EN 60068-2-6 20 g (10...2000 Hz)   |
| MTTF                          | [years]         | 180  |
| UL approval                   |                 | UL approval no. I004<br>File number UL E174189   |
| Mechanical data               |                 |  |
| Weight                        | [g]             | 268  |
| Housing                       |                 | cylindrical  |
| Dimensions                    | [mm]            | Ø 34 / L = 133.4   |
| Materials                     |                 | stainless steel (316L/1.4404); stainless steel (301/1.4310); PBT-GF20; PBT-GF30  |
| Materials (wetted parts)      |                 | stainless steel (316L/1.4404)  |
| Process connection            |                 | threaded connection 1/2" NPT external thread   |
| Probe diameter                | [mm]            | 5  |
| Installation length EL        | [mm]            | 26.6   |
| Displays / operating elements |                 |  |
| Display                       | Display unit    | 6 x LED, green (% , fps, gpm, cfm, °F, 10 <sup>3</sup> )   |
|                               | measured values | alphanumeric display, red/green 4-digit  |

# SA6014



## Flow sensor

SAN12XDB50KG/US-100


| Remarks       |  |
|---------------|--|
| Remarks       | MW = measured value                      |
|               | MEW = Final value of the measuring range |
| Pack quantity | 1 pcs.                                   |

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1: colours to DIN EN 60947-5-2  
analogue output Temperature monitoring  
OUT2: analogue output volumetric flow quantity monitoring  
Core colours :  
BK = black  
BN = brown  
BU = blue  
WH = white