


# SBN257



Flow meter with integrated backflow prevention and display

SBN32IFFRKG



CE CRN cUL us LISTED IO-Link

## Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
Measuring range	60...3000 gph   1...50 gpm
Process connection	threaded connection 1 1/2" NPT
<b>Application</b>	
Special feature	Gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; coolants
Note on media	oil 1 with viscosity: 10 mm <sup>2</sup> /s (104 °F) oil 2 with viscosity: 46 mm <sup>2</sup> /s (104 °F)
Medium temperature [°F]	14...212
Pressure rating [bar]	25
Pressure rating [MPa]	2.5
MAWP (for applications according to CRN) [bar]	25

## Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes

# SBN257



## Flow meter with integrated backflow prevention and display

SBN32IF0FRKG

Power-on delay time

[s]

< 3

### Inputs / outputs

Number of inputs and outputs

Number of digital outputs: 2; Number of analogue outputs: 1

### Outputs

Total number of outputs

2

Output signal

switching signal; analogue signal; frequency signal; IO-Link; (configurable)

Number of digital outputs

2

Output function

normally open / normally closed; (parameterisable)

Max. voltage drop switching output DC [V]

2

Permanent current rating of switching output DC [mA]

150; (per output 2 x 200 (...140 °F); 2 x 250 (...104 °F))

Switching cycles (mechanical)

10 million

Number of analogue outputs

1

Analogue current output [mA]

4...20

Max. load [Ω]

500

Short-circuit protection

yes

Overload protection

yes

Frequency of the output [Hz]

0...10000

### Measuring/setting range

Measuring range

60...3000 gph

1...50 gpm

Display range

0...3600 gph

0...60 gpm

Resolution

20 gph

0.2 gpm

Set point SP

20...3000 gph

0.4...50 gpm

Reset point rP

0...2980 gph

0...49.6 gpm

Frequency end point, FEP

200...3000 gph

3.4...50 gpm

In steps of

20 gph

0.2 gpm

Frequency at the end point FRP [Hz]

10...10000

Measuring dynamics

1:50

### Temperature monitoring

Measuring range [°F]

14...212

Display range [°F]

-26...252

Resolution [°F]

2

Set point SP [°F]

16...212

Reset point rP [°F]

14...210

In steps of [°F]

2

Frequency start point, FSP [°F]

14...172

Frequency end point, FEP [°F]

54...212

Frequency at the end point FRP [Hz]

10...10000

### Accuracy / deviations

Flow monitoring

Accuracy (in the measuring range)

$\pm (4 \% \text{ MW} + 1 \% \text{ MEW})$ ; ( $Q > 1 \text{ l/min}$ ; medium and operating temperature:  $+71,6 \text{ }^{\circ}\text{F} \pm 4\text{K}$ )

# SBN257



## Flow meter with integrated backflow prevention and display

SBN32IF0FRKG		
Repeatability		± 1 % MEW
Temperature monitoring		
Temperature drift		0,9802 °F / K
Accuracy	[K]	3 K (77 °F; Q > 1 l/min)
<b>Response times</b>		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
Damping for the analogue output dAA	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
<b>Software / programming</b>		
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour
<b>Interfaces</b>		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Smart Sensor: Process Data Variable; Device Identification
SIO mode		yes
Required master port type		A
Process data analogue		2
Process data binary		2
Min. process cycle time	[ms]	5
Supported DeviceIDs	Type of operation	DeviceID
	default	680
<b>Operating conditions</b>		
Ambient temperature	[°F]	32...140
Note on ambient temperature		medium temperature < 176 °F medium temperature < 212 °F: 32...104 °F
Storage temperature	[°F]	5...176
Protection		IP 65; IP 67
<b>Tests / approvals</b>		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
UL approval		UL Approval no.
Pressure Equipment Directive		1007 Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
<b>Mechanical data</b>		
Weight	[g]	2258.35

# SBN257



## Flow meter with integrated backflow prevention and display

SBN32IF0FRKG

Materials

stainless steel (316L/1.4404); PBT+PC-GF30;  
PBT-GF20; PC; brass chemically nickel-plated

Materials (wetted parts)

stainless steel (316 / 1.4401); stainless steel (316L/1.4404);  
brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM

Process connection

threaded connection 1 1/2" NPT

## Displays / operating elements

Display

Display unit

3 x LED, green

switching status

2 x LED, yellow

measured values

alphanumeric display, red/green 4-digit

programming

alphanumeric display, 4-digit

## Remarks

Remarks

Recommendation: use a 200-micron filter.

All data refer to water (68 °F).

MW = measured value

MEW = Final value of the measuring range

Pack quantity

1 pcs.

## Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



## Flow meter with integrated backflow prevention and display

SBN32IF0FRKG

Connection



### OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

### OUT2:


- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

- BK = black  
BN = brown  
BU = blue  
WH = white

## Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity