


VSE100



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS



Product characteristics	
Frequency range	[Hz] 0.1...12000
Communication interface	Ethernet
Application	
Design	housing for DIN rail mounting, parameter setting via PC software, VES004
Application	continuous vibration monitoring
Electrical data	
Operating voltage tolerance	[%] 20
Operating voltage	[V] 24 DC; (when using the IEPE input: 24 V + 20%; IEPE = Integrated Electronics Piezo Electric)
Current consumption	[mA] 200; (24 V)
Protection class	III
Inputs / outputs	
Total number of inputs and outputs	16; (configurable)
Number of inputs and outputs	Number of digital inputs: 8; Number of analogue inputs: 2; number of dynamic inputs: 4; Number of digital outputs: 10; Number of analogue outputs: 1
Inputs	
Total number of inputs	10
Number of digital inputs	8; (configurable)
Input circuit of digital inputs	HTL
Number of analogue inputs	2



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Analogue input (current)	[mA]	4...20
Resolution of analogue input		12
Number of dynamic inputs		4
Dynamic input - signal		0...10 mA / IEPE / 4...20 mA
Dynamic input - resolution	[bit]	16
Dynamic input - frequency range	[Hz]	0,1...10000
Dynamic input - sampling rate	[kSamples]	100

Outputs		
Total number of outputs		10
Output signal		switching signal; analogue signal
Electrical design		PNP
Number of digital outputs		10; (configurable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	100
Number of analogue outputs		1; (configurable)
Analogue current output	[mA]	0...22; (0...10 V)
Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range		
Frequency range	[Hz]	0.1...12000

Interfaces		
Communication interface		Ethernet
Protocol		TCP/IP

Operating conditions		
Ambient temperature	[°C]	0...70
Storage temperature	[°C]	0...70
Protection		IP 20

Tests / approvals		
EMC		EN IEC 61000-6-2
		EN IEC 61000-6-4
MTTF	[years]	89
UL approval	Ta	70 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current

Mechanical data		
Weight	[g]	460.6
Type of mounting		mounting on DIN rail; (TH35 (EN 60715))

VSE100



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Dimensions	[mm]	114.2 x 50 x 105.3
Materials		PA
Data memories		
History memory		yes
Data memory buffered		yes
Data memory type		ring memory; FIFO
Real-time clock		yes
Memory location		internal
Memory interval		min. 1 min
Memory size		881664 data records
Accessories		
Accessories (optional)		cross-over Ethernet patch cable for the direct connection to the PC
Remarks		
Pack quantity		1 pcs.



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Electrical connection

COMBICON: ; Maximum cable length: 250 m

Connection

