


# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100



| Product characteristics      |   |
|------------------------------|---|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analogue outputs: 1                               |
| Measuring range              | 80...9600 gph 1.3...160 gpm   |
| Process connection           | threaded connection 2" NPT internal thread DN50   |
| Application                  |   |
| Special feature              | Gold-plated contacts  |
| Application                  | totaliser function; empty pipe detection; for industrial applications                     |
| Media                        | conductive liquids; water; hydrous media  |
| Note on media                | conductivity: $\geq 20 \mu\text{S/cm}$<br>viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C) |

# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

|  |       |          |         |         |
|--|-------|----------|---------|---------|
| Medium temperature                     | [°F]  | 14...176 |         |         |
| Pressure rating                        |       | 16 bar   | 232 psi | 1.6 MPa |
| MAWP for applications according to CRN | [bar] | 16       |         |         |

### Electrical data

|                             |      |                            |  |  |
|-----------------------------|------|----------------------------|--|--|
| Operating voltage           | [V]  | 18...32 DC; (to SELV/PELV) |  |  |
| Current consumption         | [mA] | < 150                      |  |  |
| Protection class            |      | III                        |  |  |
| Reverse polarity protection |      | yes                        |  |  |
| Power-on delay time         | [s]  | 5                          |  |  |

### Inputs / outputs

|                              |   |  |  |
|------------------------------|---|--|--|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analogue outputs: 1 |  |  |
|------------------------------|---|--|--|

### Inputs

|        |               |
|--------|---------------|
| Inputs | counter reset |
|--------|---------------|

### Outputs

|   |  |                    |  |
|---|--|--------------------|--|
| Total number of outputs                         | 2  |                    |  |
| Output signal                                   | switching signal; analogue signal; pulse signal; frequency signal; IO-Link; (configurable) |                    |  |
| Electrical design                               | PNP/NPN  |                    |  |
| Number of digital outputs                       | 2  |                    |  |
| Output function                                 | normally open / normally closed; (parameterisable)   |                    |  |
| Max. voltage drop switching output DC           | [V]  | 2                  |  |
| Permanent current rating of switching output DC | [mA]   | 250; (per output)  |  |
| Number of analogue outputs                      | 1  |                    |  |
| Analogue current output                         | [mA]   | 4...20; (scalable) |  |
| Max. load                                       | [Ω]  | 500                |  |
| Analogue voltage output                         | [V]  | 0...10; (scalable) |  |
| Min. load resistance                            | [Ω]  | 2000               |  |
| Pulse output                                    |  | flow rate meter    |  |
| Short-circuit protection                        |  | yes                |  |
| Type of short-circuit protection                |  | pulsed             |  |
| Overload protection                             |  | yes                |  |
| Frequency of the output                         | [Hz]   | 0.1...10000        |  |

### Measuring/setting range

|                          |                    |                 |
|--------------------------|--------------------|-----------------|
| Measuring range          | 80...9600 gph      | 1.3...160 gpm   |
| Display range            | -11520...11520 gph | -190...190 gpm  |
| Resolution               | 5 gph              | 0.1 gpm         |
| Set point SP             | 130...9600 gph     | 2.1...160 gpm   |
| Reset point rP           | 80...9550 gph      | 1.3...159.2 gpm |
| Analogue start point ASP | 0...7680 gph       | 0...128 gpm     |
| Analogue end point AEP   | 1920...9600 gph    | 32...160 gpm    |
| Low flow cut-off LFC     | < 240 gph          | < 4 gpm         |
| In steps of              | 5 gph              | 0.1 gpm         |
| Measuring dynamics       | 1:120              |                 |

# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

| Volumetric flow quantity monitoring |  |
|-------------------------------------|--|
| Pulse value                         | 0.02...160 E06 gal   |
| In steps of                         | 0.02 gal   |
| Pulse length [s]                    | 0,008...2  |
| Temperature monitoring              |  |
| Measuring range [°F]                | -4...176   |
| Display range [°F]                  | -40...212  |
| Resolution [°F]                     | 0.5  |
| Set point SP [°F]                   | -2...176   |
| Reset point rP [°F]                 | -3...175   |
| Analogue start point [°F]           | -4...140   |
| Analogue end point [°F]             | 32...176   |
| In steps of [°F]                    | 0.5  |
| Accuracy / deviations               |  |
| Flow monitoring                     |  |
| Accuracy (in the measuring range)   | ± (0,8 % MW + 0,5 % MEW)   |
| Repeatability                       | ± 0,2% MEW   |
| Temperature monitoring              |  |
| Temperature drift                   | ± 0,0185 °F / K  |
| Accuracy [K]                        | ± 1 (77 °F; Q > 4 gpm)   |
| Response times                      |  |
| Flow monitoring                     |  |
| Response time [s]                   | 0.35; (dAP = 0)  |
| Delay time programmable dS, dr [s]  | 0...50   |
| Damping process value dAP [s]       | 0...5  |
| Temperature monitoring              |  |
| Dynamic response T05 / T09 [s]      | T09 = 3 (Q > 4 gpm)  |
| Software / programming              |  |
| Parameter setting options           | Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; switching logic; current/voltage/frequency/pulse output; start-up delay; display can be deactivated; Display unit; empty pipe detection |
| Interfaces                          |  |
| Communication interface             | IO-Link  |
| Transmission type                   | COM2 (38,4 kBaud)  |
| IO-Link revision                    | 1.1  |
| SDCI standard                       | IEC 61131-9 CDV  |
| Profiles                            | Smart Sensor - SSP 0      Generic Profiled Sensor  |
| Function                            | Device identification  |
| Function                            | Process data variable  |
| SIO mode                            | yes  |
| Required master port type           | A  |
| Process data analogue               | 3  |

# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

|                              |                          |                 |
|------------------------------|--------------------------|-----------------|
| Process data binary          |                          | 2               |
| Min. process cycle time [ms] |                          | 5               |
| Supported DeviceIDs          | <b>Type of operation</b> | <b>DeviceID</b> |
|                              | default                  | 390             |

| Operating conditions     |  |              |
|--------------------------|--|--------------|
| Ambient temperature [°F] |  | 14...140     |
| Storage temperature [°F] |  | -13...176    |
| Protection               |  | IP 65; IP 67 |

| Tests / approvals            |   |                    |
|------------------------------|---|--------------------|
| EMC                          | DIN EN 60947-5-9  |                    |
| Shock resistance             | DIN EN 60068-2-27   | 20 g (11 ms)       |
| Vibration resistance         | DIN EN 60068-2-6  | 5 g (10...2000 Hz) |
| MTTF [years]                 |   | 85                 |
| UL approval                  | UL approval no.   | I008               |
|                              | File number UL  | E174189            |
| Pressure Equipment Directive | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request |                    |

| Mechanical data          |  |                 |
|--------------------------|--|-----------------|
| Weight [g]               |  | 2643            |
| Housing                  |  | rectangular     |
| Dimensions [mm]          |  | 180 x 103 x 117 |
| Materials                | stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEI; FKM; PBT-GF20; TPE-U |                 |
| Materials (wetted parts) | stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEEK; FKM                 |                 |
| Process connection       | threaded connection 2" NPT internal thread DN50  |                 |

| Displays / operating elements |                  |   |
|-------------------------------|------------------|---|
| Display                       | Display unit     | 6 x LED, green (gpm, gph, gal, °F, 10 <sup>3</sup> , 1000 x 10 <sup>3</sup> ) |
|                               | switching status | 2 x LED, yellow   |
|                               | measured values  | alphanumeric display, 4-digit   |
|                               | programming      | alphanumeric display, 4-digit   |

| Accessories    |  |       |
|----------------|--|-------|
| Items supplied |  | Label |

| Remarks       |  |        |
|---------------|--|--------|
| Remarks       | MW = measured value                      |        |
|               | MEW = Final value of the measuring range |        |
| Pack quantity |  | 1 pcs. |

## Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

### Connection



|       |  |
|-------|--|
| OUT1: | colours to DIN EN 60947-5-2<br>switching output empty pipe detection<br>switching output volumetric flow quantity monitoring<br>frequency output volumetric flow quantity monitoring<br>Pulse output quantity meter<br>signal output Preset counter<br>IO-Link                     |
| OUT2: | switching output empty pipe detection<br>switching output volumetric flow quantity monitoring<br>switching output Temperature monitoring<br>analogue output volumetric flow quantity monitoring<br>analogue output Temperature monitoring<br>input counter reset<br>Core colours : |
| BK =  | black  |
| BN =  | brown  |
| BU =  | blue   |
| WH =  | white  |

# SM2601




## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity