


Coaxial pipe for level sensors

LR COAX TUBE NPT L240



CRN

Application		
Design		for level sensors LR
Medium temperature	[°C]	-40...200
Pressure rating	[bar]	16
Vacuum resistance	[mbar]	-1000
MAWP (for applications according to CRN)	[bar]	16
Mechanical data		
Weight	[g]	188.5
Materials		Coaxial pipe: stainless steel (304/1.4301); fixing bracket: stainless steel (301/1.4310); Centring piece: PPS reinforced fibre
Sensor connection		threaded connection G 3/4 internal thread
Process connection		threaded connection 3/4" NPT external thread
Length L	[mm]	240
Remarks		
Pack quantity		1 pcs.