




Flow monitor

SCR14ABAFPKG/US-100-IPF

Article no longer available - archive entry

Alternative articles: SI5010 + E40099
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		G 1/4 external thread
Application		
Media		Liquids
Medium temperature	[°C]	10...50
Pressure rating	[bar]	30
Liquids		
Medium temperature	[°C]	10...50
Electrical data		
Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal



Flow monitor

SCR14ABAFPKG/US-100-IPF

Electrical design	PNP
Number of digital outputs	1
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	400
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Liquids	
Setting range [cm/s]	100...500

Accuracy / deviations

Temperature gradient [K/min]	1
------------------------------	---

Response times

Response time [s]	1...2
-------------------	-------

Liquids	
Response time [s]	1...2

Software / programming

Adjustment of the switch point	potentiometer
--------------------------------	---------------

Operating conditions

Ambient temperature [°C]	10...50
Protection	IP 67

Mechanical data

Materials	PBT-GF20
Materials (wetted parts)	stainless steel (303/1.4305)
Process connection	G 1/4 external thread

Displays / operating elements

Display	function	11 x LED
---------	----------	----------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



ST0526



Flow monitor

SCR14ABAFPKG/US-100-IPF

Connection

