




Control monitor for flow sensors

VS0200/110VAC

Article no longer available - archive entry

Alternative articles: SN0150  
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application	Flow monitoring; Wire monitoring	
Electrical data		
Operating voltage tolerance	[%]	-10...10
Operating voltage	[V]	< 110 AC
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Total number of outputs		2
Electrical design		relay
Switching function flow monitoring		relay energised when flow is present
Switching function wire break monitoring		relay de-energised in case of wire break and short circuit
Response times		
Response time	[s]	< 10
Software / programming		
Adjustment of the switch point		potentiometer
Selection liquids / gases		slide switch
Operating conditions		
Ambient temperature	[°C]	0...60



Control monitor for flow sensors

VS0200/110VAC

Protection	IP 40
Protection rating terminals	IP 20

Mechanical data

Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110
Materials	plastics

Displays / operating elements

Display	function	11 x LED
	switching status	LED, red


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Wire monitoring
- 2: Relais Flow monitoring
- Core colours :
- BN = brown
- BU = blue
- BK = black
- WH = white
- GY = grey