
TS2454

Temperature cable sensor with process connection

TS-200KLKD06 .../US



1 connection area, see remark

DNV
DNV.COM/AF

Product characteristics			
Measuring range		-100...600 °C	-148...1112 °F
Process connection		diameter Ø 6 mm	
Installation length EL	[mm]	200; (medium temperatures < 200 °C: 250)	
Application			
Measuring element		1 x Pt 100; (to DIN EN 60751, class A)	
Media		liquids and gases	
Minimum installation depth	[mm]	15	
Electrical data			
Protection class		III	
Measuring/setting range			
Probe length L	[mm]	250	
Measuring range		-100...600 °C	-148...1112 °F
Accuracy / deviations			
Accuracy	[K]	± (0,15 K + 0,002 x|t|)	
Response times			
Dynamic response T05 / T09	[s]	12 / 34; (to DIN EN 60751)	
Operating conditions			
Protection		IP 67	
Tests / approvals			
MTTF	[years]	11415.5	
Mechanical data			
Weight	[g]	101.9	
Dimensions	[mm]	Ø 6	
Materials		stainless steel (1.4571/316Ti); PFA/PTFE	
Materials (wetted parts)		stainless steel (1.4571/316Ti)	
Process connection		diameter Ø 6 mm	
Probe diameter	[mm]	6	
Installation length EL	[mm]	200; (medium temperatures < 200 °C: 250)	
Remarks			
Remarks		The values for accuracy apply to flowing water.	
Pack quantity		1 pcs.	

TS2454

Temperature cable sensor with process connection

TS-200KLKD06 .../US

Electrical connection

Cable: 2 m, PTFE; temperature resistant up to 250 °C

Connector: 1 x M12; coding: A



Connection

