




AS-Interface PLC

ControllerE 1Mstr 1RS232C

Article no longer available - archive entry



Application		
Application		decentralised controller
Electrical data		
Operating voltage	[V]	24 DC; ("supply class 2" to cULus)
Insulation rating	[V]	500
Current consumption	[mA]	< 500
Max. current consumption from AS-i	[mA]	10
Max. power consumption	[VA]	10
Number of AS-i masters		1
Electrical separation		yes
Interfaces		
Communication interface		RS232
RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Connector type		RJ11



AS-Interface PLC

ControllerE 1Mstr 1RS232C

Usage type	programming
Note on interfaces	electrically isolated

Operating conditions

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 20

AS-i classification

AS-i version	2.1
AS-i profile	M3
AS-i certificate	61101

Mechanical data

Weight	[g]	507.2
Housing		housing for DIN rail mounting
Dimensions	[mm]	86 x 131 x 107
Materials		aluminium; steel sheet galvanised

Displays / operating elements

Display	function	1 x LED, red
		2 x LED, green
		2 x LED, yellow
		full graphic LCD display

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connection

