
AL1321

IO-Link master with EtherNet/IP interface

IO-Link Master DL EIP 4P IP69K

Alternative articles: AL1325

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		hygienic systems; I/O modules for field applications
Daisy-chain function		fieldbus interface
Electrical data		
Operating voltage	[V]	20...28 DC; (US ; to SELV/PELV)
Current consumption	[mA]	300...3900; (US)
Protection class		III
Sensor supply US		
Max. current load total	[A]	3.6
Inputs / outputs		
Total number of inputs and outputs		8; (configurable)
Number of inputs and outputs		Number of digital inputs: 8; Number of digital outputs: 4
Inputs		
Number of digital inputs		8; (IO-Link Port Class A: 4 x 2)

AL1321

IO-Link master with EtherNet/IP interface

IO-Link Master DL EIP 4P IP69K

Switching level high	[V]	11...28	
Switching level low	[V]	0...5	
Digital inputs protected against short circuits		yes	
Outputs			
Number of digital outputs		4; (IO-Link Port Class A: 4 x 1)	
Max. current load per output	[mA]	300	
Short-circuit proof		yes	
Interfaces			
Communication interface		Ethernet; IO-Link	
Ethernet - EtherNet/IP			
Transmission standard		10Base-T; 100Base-TX	
Transmission rate		10 MBit/s; 100 MBit/s	
Protocol		EtherNet/IP	
Factory settings		IP address: 192.168.1.250	
		subnet mask: 255.255.255.255	
		gateway IP address: 0.0.0.0	
		MAC address: see type label	
Note on interfaces		DHCP, BOOTP, static	
		DLR (Device Level Ring)	
		Supported network topologies: line	
		ring	
Ethernet - Internet of Things			
Transmission standard		10Base-T; 100Base-TX	
Transmission rate		10 MBit/s; 100 MBit/s	
Protocol		MQTT JSON	
Factory settings		IP address: 169.254.x.x	
		subnet mask: 255.255.0.0	
		gateway IP address: 0.0.0.0	
		MAC address: see type label	
Note on interfaces		Secure protocol: HTTPS	
IO-Link Master			
Transmission type		COM1 (4,8 kBaud); COM2 (38,4 kBaud); COM3 (230,4 kBaud)	
IO-Link revision		1.1	
Number of ports class A		4	
Operating conditions			
Ambient temperature	[°C]	-25...60	
Storage temperature	[°C]	-25...85	
Max. relative air humidity	[%]	90	
Protection		IP 65; IP 66; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K)	
Protection rating (NEMA 250)		6P	
Pollution degree		2	
Chemical media		ISO 16750-5	HLP, CC, DB, DC, DD, CA
		NEMA 250 5.13.1	AA

AL1321

IO-Link master with EtherNet/IP interface

IO-Link Master DL EIP 4P IP69K

Tests / approvals			
EMC		EN 61000-6-2	
		EN 61000-6-4	
Shock resistance		DIN EN 60068-2-27	
Vibration resistance		DIN EN 60068-2-64 2009-04	
		DIN EN 60068-2-6 2008-10	
MTTF	[years]	95	

Mechanical data		
Weight	[g]	283.5
Materials		housing: PA grey; socket: stainless steel (1.4404 / 316L)
Sealing material		EPDM

Accessories	
Items supplied	Protective cap: 1 x M12, stainless steel, E12542

Remarks	
Remarks	For further information please see the operating instructions.
Pack quantity	1 pcs.

Electrical connection - Ethernet

Connector: M12; coding: D; Sealing: EPDM




EtherNet/IP X21, X22	
1	TX +
2	RX +
3	TX -
4	RX -
5	not used

IoT X23	
1	TX +
2	RX +
3	TX -
4	RX -
5	not used

Electrical connection - Process connection

Connector: M12; coding: A; Sealing: EPDM



AL1321

IO-Link master with EtherNet/IP interface

IO-Link Master DL EIP 4P IP69K

IO-Link Port Class A X01...X04	
1	Sensor supply (US) L+
2	digital input
3	Sensor supply (US) L-
4	C/Q IO-Link
5	not used

Electrical connection - power supply

Connector: M12; coding: A



X31	
1	+ 24 V DC (US)
2	not used
3	GND (US)
4	not used