


CR1080



Programmable graphic display for controlling mobile machines

R360/PDM NG/DialogDisplay



Electrical data

Operating voltage	[V]	10...32 DC
Power consumption	[W]	7.2

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 1; Number of analogue inputs: 1; Number of digital outputs: 1
------------------------------	---

Inputs

Number of digital inputs		1
Number of analogue inputs		1
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	0...32

Outputs

Number of digital outputs	1
---------------------------	---

Software / programming

PLC function to IEC 61131-3	yes
-----------------------------	-----

Interfaces

Number of CAN interfaces	4
Number of Ethernet interfaces	1
Number of USB interfaces	2

Mechanical data

Weight	[g]	1747.4
Type of mounting	panel / surface	

CR1080



Programmable graphic display for controlling mobile machines

R360/PDM NG/DialogDisplay

Dimensions	[mm]	145 x 225 x 80
------------	------	----------------

Displays / operating elements

Display		7" colour display
Operating elements	9	freely programmable backlit function keys
	1	encoder with pushbutton
Display resolution		800 x 480
Display type		colour display
Display size		7"
Display background illumination		LED

Data memories

Real-time clock		yes
-----------------	--	-----

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12		
--------------------	--	--