
PI3658

Flush pressure sensor with display

PI-,25-REA01-KFPKG/US/ /P

Article no longer available - archive entry



1 7-segment LED display
2 programming button

CE

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Measuring range	[mbar]	0...250
Process connection		threaded connection G 1 external thread
Application		
Special feature		Gold-plated contacts
Application		flush mountable for the food and beverage industry
Installation		freely rotatable housing 350°
Media		viscous media and liquids with suspended particles; liquids and gases
Medium temperature	[°C]	-25...125; (145 max. 1h)
Min. bursting pressure	[mbar]	30000
Pressure rating	[mbar]	10000
Type of pressure		relative pressure
No dead space		yes
Electrical data		
Operating voltage	[V]	20...30 DC

PI3658

Flush pressure sensor with display

PI-,25-REA01-KFPKG/US/ /P

Current consumption	[mA]	< 60
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; (configurable)
Electrical design		PNP
Number of digital outputs		1
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range	[mbar]	0...250
Set point SP	[mbar]	2...250
Reset point rP	[mbar]	1...248
In steps of	[mbar]	1
Accuracy / deviations		
Switch point accuracy [% of the final value]		< ± 1,5
Repeatability [% of the final value]		< ± 0,25; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the final value]		< ± 1,0
Temperature drift per 10 K		< ± 0.4

Response times

Switching frequency for a given set response time of one output

Response time (dAP)	[ms]	3	6	10	17	30	60	125	250	500
Switching frequency	[Hz]	170	80	50	30	16	8	4	2	1

Response time	[ms]	at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %
Delay time programmable dS, dr	[s]	0, 0,2,...10, 11,...50

PI3658

Flush pressure sensor with display

PI-,25-REA01-KFPKG/US/ /P

Max. response time analogue output [ms]	3	
Software / programming		
Adjustment of the switch point	programming button	
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping	
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 67	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Materials	stainless steel (1.4404 / 316L); PBT; PC; PA; EPDM/X; FKM	
Materials (wetted parts)	stainless steel (1.4404 / 316L); ceramics; PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1 external thread	
Displays / operating elements		
Display	switching status	LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Remarks		
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



PI3658

Flush pressure sensor with display

PI-,25-REA01-KFPKG/US/ /P

Connection

