




Compact evaluation unit for speed monitoring

DIA2010-ZROA/50-3000 I/MIN/10M

Article no longer available - archive entry



Product characteristics		
Output function		normally open
Sensing range	[mm]	10
Dimensions	[mm]	M30 x 1.5 / L = 81
Application		
Application		simple evaluation of rotating and linear movement with regard to underspeed; blocking
Electrical data		
Nominal voltage AC	[V]	20...250
Nominal voltage DC	[V]	20...250
Reverse polarity protection		no
Outputs		
Total number of outputs		1
Output function		normally open
Max. voltage drop switching output DC	[V]	6.5
Minimum load current	[mA]	6
Max. leakage current	[mA]	1.5
Permanent current rating of switching output AC	[mA]	250; (350 AC (...50 °C))
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	2200
Short-circuit proof		no
Overload protection		no
Detection zone		
Sensing range	[mm]	10
Sensing range adjustable		no

DI0003



Compact evaluation unit for speed monitoring

DIA2010-ZROA/50-3000 I/MIN/10M

Measuring/setting range		
Setting range	[Imp/min]	50...3000
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
Response times		
Start-up delay	[s]	12
Max. damping frequency	[Imp/min]	4000
Software / programming		
Adjustment of the switch point		multiturn potentiometer
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Mechanical data		
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation		M30 x 1.5
Materials		brass special coating; PBT
Tightening torque	[Nm]	50
Displays / operating elements		
Display	switching status	1 x LED, green
Remarks		
Remarks		Recommendation Check the safe functioning of the unit after a short circuit.

DI0003



Compact evaluation unit for speed monitoring

DIA2010-ZROA/50-3000 I/MIN/10M

Electrical connection

Cable: 10 m, PVC; 2 x 0.5 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1 \leq 2 A (fast acting)

Core colours :

BN = brown

BU = blue