


## Connecting cable with socket

ADOAH043MSS0015H04

Please see the technical note under "Downloads"



## Application

Special feature	Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Free from silicone	yes

## Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Max. current load total [A]	4

## Outputs

Electrical design	PNP
-------------------	-----

## Operating conditions

Ambient temperature [°C]	-25...90
Note on ambient temperature	cULus: ...75
Ambient temperature (moving) [°C]	-25...90
Note on ambient temperature (moving)	cULus: ...75
Protection	IP 65; IP 67; IP 68; IP 69K

## Tests / approvals

MTTF [years]	20027
--------------	-------

## Mechanical data

Weight [g]	493
Dimensions [mm]	26.5 x 15.5 x 36.5



## Connecting cable with socket

ADOAH043MSS0015H04

Materials	housing: TPU black transparent; Sealing: FKM	
Material nut	brass, nickel-plated	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>
	bending cycles	> 5 Mio.
	torsional strain	± 180 °/m

## Displays / operating elements

Display	switching status	1 x LED, yellow
	switching status	1 x LED, white
	operation	1 x LED, green

## Remarks


Notes	Please see the technical note under "Downloads"
Pack quantity	1 pcs.

## Electrical connection


Cable: 15 m, PUR, Halogen-free, black, Ø 4.3 mm; 4 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

## Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



## Connection



	Core colours :
BK =	black
BN =	brown
WH =	white
BU =	blue
YE =	yellow
GN =	green