




Sensor for point level detection

LI0273--K-00KNPKG/US

Article no longer available - archive entry

Alternative articles: LI5142

When selecting an alternative article and accessories please note that technical data may differ!



1 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Probe length L [mm]	273

Application

Special feature	Gold-plated contacts
Media	coolants; oils
Cannot be used for	acids; alkali
Medium temperature [°C]	0...65; (For water and hydrous media with temperatures > 35 °C install the unit into a climatic tube.)
Tank pressure [bar]	0.5; (when mounting with mounting accessories: E43001 - E43007, E43019)

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	13; (24 V)
Protection class	II
Reverse polarity protection	yes
Measuring principle	capacitive

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250

LI5042



Sensor for point level detection

LI0273--K-00KNPKG/US

Switching frequency DC	[Hz]	5
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	273
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	15 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV coupling clamp
	EN 61000-4-6 HF conducted	10 V (500 Ω AC)
Mechanical data		
Dimensions	[mm]	Ø 16
Materials		PP; TPE-V
Materials (wetted parts)		PP
Displays / operating elements		
Display	operation	1 x LED, green
	switching status	1 x LED, yellow
	unsafe zone	1 x LED, red
Remarks		
Pack quantity		1 pcs.

LI5042



Sensor for point level detection

LI0273--K-00KNPKG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated

