

MK5030




Cylinder sensor for clean line cylinders

MKR3000-ANKG/AS

Article no longer available - archive entry

Alternative articles: MK5112

When selecting an alternative article and accessories please note that technical data may differ!



1 Sensing face



Product characteristics

Electrical design	NPN
Output function	normally open
Dimensions [mm]	12 x 30 x 12

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Response sensitivity [mT]	3
Travel speed [m/s]	< 5

Accuracy / deviations

Hysteresis [mm]	1
Repeatability [mm]	0.1

Operating conditions

Ambient temperature [°C]	-25...75
--------------------------	----------

MK5030



Cylinder sensor for clean line cylinders

MKR3000-ANKG/AS

Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)	
Mechanical data		
Sensing face	front	
Cylinder type	clean line cylinders	
Dimensions [mm]	12 x 30 x 12	
Materials	aluminium; plastics	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity	1 pcs.	
Electrical connection - plug		

Connector: 1 x M8; coding: A



Connection

