


N7S21A



Inductive NAMUR slot sensor

I7S23,5-N /1G/1D



Product characteristics

Electrical design	NAMUR
Output function	normally closed
Housing	rectangular
Dimensions [mm]	19 x 10 x 15

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: $U = 15 \text{ V}$ / $I = 50 \text{ mA}$ / $P = 120 \text{ mW}$
Nominal voltage DC [V]	8.2; (1k Ω)
Supply voltage DC [V]	5...25; (when used outside the hazardous area)
Current consumption [mA]	< 1.2; (disabled; conductive: > 2,1)
Protection class	III

Outputs

Electrical design	NAMUR
Output function	normally closed
Switching frequency DC [Hz]	3000

Detection zone

Insertion depth (from the side) [mm]	5...7
--------------------------------------	-------

Accuracy / deviations

Hysteresis [%]	0...0.05
----------------	----------

Operating conditions

Ambient temperature [°C]	-40...100
Protection	IP 67

Tests / approvals

Approval	BVS 08 ATEX E026; IECEx BVS 09.0016
----------	-------------------------------------

N7S21A



Inductive NAMUR slot sensor

I7S23,5-N /1G/1D

ATEX marking	II 1G Ex ia IIC T4 Ga	
	II 1D Ex ia IIIC T125°C Da	
EMC	EN 60947-5-2	
MTTF [years]		2942

Safety classification

Max. internal capacitance [nF]	150
Max. internal inductance [μH]	150

Mechanical data

Weight [g]	34
Housing	rectangular
Dimensions [mm]	19 x 10 x 15
Slot width [mm]	3.5
Materials	PBT

Accessories

Items supplied	counter-sunk screw: 1 x M1,6 x 10, stainless steel
	Hexagon nut: 1 x M1,6


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.065 m; 2 x 0.14 mm², PTFE

Connector: 1 x DUBOX



Connection

