


External illumination

Dome Light 130 WH IR/ US

**Product characteristics**


Type of light	white light; infrared light	
Application		
Illuminated field [mm]		130 x 130
Design		Dome
Type of operation	normal light intensity (permanent operation possible); High light intensity (pulsed)	
Electrical data		
Operating voltage [V]		24 DC
Current consumption [mA]	operating mode "permanent operation": 540; operating mode "high light intensity": 2580	
Protection class	III; (PELV)	
Type of light	white light; infrared light	
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 1	
Inputs		
Trigger	24 V PNP/NPN; external	

O2D932



External illumination

Dome Light 130 WH IR/ US

Number of digital inputs		1
Operating conditions		
Ambient temperature	[°C]	-10...40
Storage temperature	[°C]	-20...60
Protection		IP 65
Tests / approvals		
Photobiological safety		risk group 1; (DIN EN 62471)
Mechanical data		
Weight	[g]	1018.15
Dimensions	[mm]	256.8 x 197 x 106.8
Materials		housing: aluminium black anodised; Cover: ABS
Tightening torque	[Nm]	0.5...1.5
Displays / operating elements		
Display	operation	1 x LED, green
	operating mode "high light intensity"	1 x LED, red
	LED segment	1 x LED, white
Remarks		
Pack quantity		1 pcs.
Electrical connection - parameter setting		
Connector:	M12; coding:	A
		
1:	operating mode "high light intensity"	
2:	colour 2	
3:	GND	
4:	LED segment 1	
5:	LED segment 2	
6:	LED segment 3	
7:	LED segment 4	
8:	deactivate buttons	

O2D932




External illumination

Dome Light 130 WH IR/ US

Electrical connection - power supply

Connector: M12; coding: A



1:	U+
2:	trigger input NPN
3:	GND
4:	trigger input PNP
5:	dimmer