
IN5281

Inductive sensor

IN-2004-ARKG/2A/3M



1 threaded bush M3 Depth 5.8 mm
Tightening torque maximum 1.2 Nm screw fixing class 8.8
when brass insert in contact with counterpart

Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	4
Housing		rectangular
Dimensions	[mm]	40 x 12 x 26
Application		
Special feature		Halogen-free
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	4
Minimum load current	[mA]	5
Max. leakage current	[mA]	1
Short-time current rating of switching output	[mA]	2000; (only for mounting on a solid metal plate or cooling plate: 150 x 50 x 2 mm Intermittent operation with a max. switch-on time of the load current of 4 s. After that a min. switch-off time of the load current of 2 s has to be kept.)
Switching frequency DC	[Hz]	70
Detection zone		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25

IN5281


Inductive sensor

IN-2004-ARKG/2A/3M

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
MTTF	[years]	874
Mechanical data		
Weight	[g]	143
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 12 x 26
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Cable: 3 m, PUR, Halogen-free; 2 x 0.5 mm²

Connection



	Core colours :
BN =	brown
BU =	blue