




Inductive sensor

IZB30,8-BPKG/V2A/AS-514-TPS RT

phase-out article



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	0.8
Housing		cylindrical
Dimensions	[mm]	Ø 4
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	800
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



Inductive sensor

IZB30,8-BPKG/V2A/AS-514-TPS RT

Detection zone		
Sensing range	[mm]	0.8
Real sensing range Sr	[mm]	0.8 ± 10 %
Operating distance	[mm]	0...0.65
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	953
Mechanical data		
Weight	[g]	13.2
Housing		cylindrical
Mounting		flush mountable
Dimensions	[mm]	Ø 4
Materials		stainless steel (303/1.4305); LCP
Displays / operating elements		
Display	switching status	4 x 90° LED, red
Accessories		
Items supplied		Mounting clamps: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		

Connector: 1 x M8; coding: A



IZ5034



Inductive sensor

IZB30,8-BPKG/V2A/AS-514-TPS RT

Connection

