




Diffuse reflection sensor

OUT-HPKG/6M



receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	35; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	1...200; (white paper 200 x 200 mm)
Range adjustable		yes
Max. light spot diameter	[mm]	180
Light spot dimensions refer to		at maximum range

Operating conditions


Ambient temperature	[°C]	-25...80
---------------------	------	----------



Diffuse reflection sensor

OUT-HPKG/6M

Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF		[years]	685
Mechanical data			
Weight		[g]	283
Housing		rectangular	
Dimensions		[mm]	28 x 16 x 51
Materials		PPO modified	
Lens material		glass	
Lens alignment		side lens	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		Angle bracket: 1, E20211	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Cable: 6 m, PVC; 3 x 0.34 mm²			
Connection			



BN	brown
BU	blue
BK	black



Diffuse reflection sensor

OUT-HPKG/6M

Diagrams and graphs

excess gain graph

