

PM2056



Flush pressure transmitter

PM-2,5-RES30-E-ZVG/US/ /P

phase-out article


Discontinuation date: 03/31/2024

Alternative articles: PI1005 or PM1706

When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.

no more adapters available as accessories



- 1 Aseptoflex sealing edge
- 2 Aseptoflex thread



Product characteristics				
Number of inputs and outputs	Number of analogue outputs: 1			
Measuring range	-0.13...2.5 bar	-130...2500 mbar	-1.8...36.3 psi	-13...250 kPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex			
Application				
Special feature	Gold-plated contacts			
Application	flush mountable for the food and beverage industry			
Media	viscous media and liquids with suspended particles; liquids and gases			
Medium temperature [°C]	-25...125; (145 max. 1h)			
Min. bursting pressure	50 bar	725 psi	5000 kPa	
Pressure rating	20 bar	290 psi	2000 kPa	



Flush pressure transmitter

PM-2,5-RES30-E-ZVG/US/ /P

Type of pressure	relative pressure			
No dead space	yes			
Electrical data				
Operating voltage [V]	14...30 DC			
Min. insulation resistance [MΩ]	100; (500 V DC)			
Protection class	III			
Reverse polarity protection	yes			
Measuring principle	hydrostatic			
Inputs / outputs				
Number of inputs and outputs	Number of analogue outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analogue signal			
Number of analogue outputs	1			
Analogue current output [mA]	4...20			
Max. load [Ω]	550; (Ub = 24 V; (Ub - 13 V) / 20 mA)			
Overload protection	yes			
Measuring/setting range				
Measuring range	-0.13...2.5 bar	-130...2500 mbar	-1.8...36.3 psi	-13...250 kPa
Analogue start point	-0.13...1.88 bar	-1.8...27.2 psi	-13...188 kPa	
Analogue end point	0.5...2.5 bar	7.3...36.3 psi	50...250 kPa	
In steps of	0.01 bar	0.1 psi	1 kPa	
Factory setting		ASP = 0.0 bar	AEP = 2.50 bar	
Accuracy / deviations				
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)			
Characteristics deviation [% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)			
Linearity deviation [% of the span]	< ± 0,5; (Turn down 1:1)			
Hysteresis deviation [% of the span]	< ± 0,1; (Turn down 1:1)			
Long-term stability [% of the span]	< ± 0,1; (Turn down 1:1; per year)			
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,1; (0...80 °C)			
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (0...80 °C)			
Response times				
Max. response time analogue output [ms]	3			
Software / programming				
Parameter setting options	zero point; span			
Interfaces				
Communication interface	EPS			

PM2056



Flush pressure transmitter

PM-2,5-RES30-E-ZVG/US/ /P

Operating conditions

Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	1 GHz / accuracy < 2,5%
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	271

Mechanical data

Weight	[g]	472
Materials		stainless steel (316L/1.4404); PEI; FKM
Materials (wetted parts)		ceramics (99.9 % Al ₂ O ₃); stainless steel (316L/1.4404); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex

Remarks

Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.
Notes	Please do not use for new projects.; no more adapters available as accessories
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

