

PP7543



Pressure switch with ceramic measuring cell


PP-025-SBG14-QFRKG/BS/ /N

Article no longer available - archive entry

Alternative articles: PP7553

When selecting an alternative article and accessories please note that technical data may differ!

Note: electrical connection of the replacement units via M12 socket.



Product characteristics

Output signal	switching signal		
Measuring range	0...25 bar	0...363 psi	0...2.5 MPa
Process connection	threaded connection G 1/4 external thread internal thread:M5		

Application

Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-25...90; (on request: -40...90 °C)		
Min. bursting pressure	350 bar	5075 psi	35 MPa
Pressure rating	100 bar	1450 psi	10 Mpa
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	9.6...30 DC		
Current consumption [mA]	< 45		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	0.3		



Pressure switch with ceramic measuring cell

PP-025-SBG14-QFRKG/BS/ /N

Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 2		
Outputs			
Total number of outputs	2		
Output signal	switching signal		
Electrical design	PNP/NPN		
Number of digital outputs	2		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2		
Permanent current rating of switching output DC [mA]	250		
Switching frequency DC [Hz]	< 170		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	0...25 bar	0...363 psi	0...2.5 MPa
Set point SP	0.3...25 bar	4...363 psi	0.03...2.5 MPa
Reset point rP	0.2...24.9 bar	2...362 psi	0.02...2.49 MPa
In steps of	0.1 bar	1 psi	0.01 MPa
Accuracy / deviations			
Switch point accuracy [% of the span]	< ± 1,5		
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Linearity deviation [% of the span]	< ± 0,5		
Hysteresis deviation [% of the span]	< ± 0,1		
Long-term stability [% of the span]	< ± 0,1; (per year)		
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,2; (0...80 °C)		
Temperature coefficient span [% of the span / 10 K]	< ± 0,3; (0...80 °C)		
Response times			
Response time [ms]	< 3		
Damping for the switching output dAP [s]	0...4		
Software / programming			
Adjustment of the switch point	programming unit / teach function		

PP7543



Pressure switch with ceramic measuring cell

PP-025-SBG14-QFRKG/BS/ /N

Interfaces			
Communication interface		EPS	
Operating conditions			
Ambient temperature	[°C]	-40...90	
Storage temperature	[°C]	-40...100	
Protection		IP 68; (BFSL = Best Fit Straight Line; LS = limit value setting)	
Tests / approvals			
EMC	radiation of interference	according to the automotive directive 1995/54/EC	
	immunity	according to the automotive directive 1995/54/EC annex IX	
	HF radiated	150 V/m	
	pulse resistance	ISO 7637	
	supply	ISO 7637-2 (Pulse 1a, 1b, 2, 3a, 3b, 4, 6, 7)	
	signal cables	ISO 7637-3 (Pulse a und b)	
	immunity	EN 61000-6-2	
	EN 61000-4-2 ESD	8/15 kV	
	EN 61000-4-3 HF radiated	100 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	Shock resistance	DIN IEC 60068-2-27 / DIN IEC 60068-2-29	1000 g
	Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data			
Materials		stainless steel (1.4301 / 304); FKM; PBT	
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles		100 million	
Process connection		threaded connection G 1/4 external thread internal thread:M5	
Restrictor element integrated		no (can be retrofitted)	
Displays / operating elements			
Display	operation	LED, green	
	switching status	2 x LED, yellow	
Teach function		yes	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Connector: 1 x Bajonett			

PP7543



Pressure switch with ceramic measuring cell

PP-025-SBG14-QFRKG/BS/ /N

