
SBG257

Flow meter with integrated backflow prevention and display

SBG54IF0FRKG



Product characteristics			
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range		4...200 l/min	0.24...12 m³/h
Process connection		threaded connection G 1 1/4	
Application			
Special feature		Gold-plated contacts	
Application		for industrial applications	
Media		Liquids; water; glycol solutions; coolants	
Note on media		oil 1 with viscosity: 10 mm²/s (40 °C)	
		oil 2 with viscosity: 46 mm²/s (40 °C)	
Medium temperature	[°C]	-10...100	
Pressure rating	[bar]	25	
Pressure rating	[MPa]	2.5	
MAWP (for applications according to CRN)	[bar]	25	
Electrical data			
Operating voltage	[V]	18...30 DC; (to SELV/PELV)	
Current consumption	[mA]	< 50	
Protection class		III	
Reverse polarity protection		yes	

SBG257

Flow meter with integrated backflow prevention and display

SBG54IF0FRKG

Power-on delay time	[s]	< 3
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; frequency signal; IO-Link; (configurable)
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (...60 °C); 2 x 250 (...40 °C))
Switching cycles (mechanical)		10 million
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Frequency of the output	[Hz]	0...10000
Measuring/setting range		
Measuring range		4...200 l/min / 0.24...12 m³/h
Display range		0...240 l/min / 0...14.4 m³/h
Resolution		1 l/min / 0.05 m³/h
Set point SP		2...200 l/min / 0.1...12 m³/h
Reset point rP		0...198 l/min / 0...11.9 m³/h
Frequency end point, FEP		13...200 l/min / 0.8...12 m³/h
In steps of		1 l/min / 0.05 m³/h
Frequency at the end point FRP	[Hz]	10...10000
Measuring dynamics		1:50
Temperature monitoring		
Measuring range	[°C]	-10...100
Display range	[°C]	-32...122
Resolution	[°C]	1
Set point SP	[°C]	-9...100
Reset point rP	[°C]	-10...99
In steps of	[°C]	1
Frequency start point, FSP	[°C]	-10...78
Frequency end point, FEP	[°C]	12...100
Frequency at the end point FRP	[Hz]	10...10000
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (4 % MW + 1 % MEW); (Q > 1 l/min; medium and operating temperature: +22 °C ± 4K)

SBG257

Flow meter with integrated backflow prevention and display

SBG54IF0FRKG

Repeatability		± 1 % MEW	
Temperature monitoring			
Temperature drift		0,029 °C / K	
Accuracy	[K]	3 K (25°C; Q > 1 l/min)	
Response times			
Flow monitoring			
Response time	[s]	0.01	
Damping process value dAP	[s]	0...5	
Damping for the analogue output dAA	[s]	0...5	
Temperature monitoring			
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)	
Software / programming			
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/frequency output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9 CDV	
Profiles		Smart Sensor: Process Data Variable; Device Identification	
SIO mode		yes	
Required master port type		A	
Process data analogue		2	
Process data binary		2	
Min. process cycle time	[ms]	5	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	564
Operating conditions			
Ambient temperature	[°C]	0...60	
Note on ambient temperature		medium temperature < 80 °C	
		medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	145	
UL approval		UL Approval no.	I007
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	1977.5	

SBG257

Flow meter with integrated backflow prevention and display

SBG54IF0FRKG

Materials	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated	
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; PP-GF30; spacer: POM; O-ring: FKM	
Process connection	threaded connection G 1 1/4	
Displays / operating elements		
Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
	programming	alphanumeric display, 4-digit
Remarks		
Remarks	Recommendation: use a 200-micron filter.	
	All data refer to water (20 °C).	
	MW = measured value	
	MEW = Final value of the measuring range	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




SBG257

Flow meter with integrated backflow prevention and display

SBG54IF0FRKG

Connection



OUT1:
- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link


OUT2:
- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring

colours to DIN EN 60947-5-2
Core colours :

BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity