
SD6000

Compressed air meter

SDR12DGXFPKG/US-100

phase-out article
Discontinuation date: 12/31/2024

Alternative articles: SD6500
When selecting an alternative article and accessories please note that technical data may differ!



1 alphanumeric display 4-digit
2 programming buttons

Product characteristics			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	10...1250 l/min	0.3...103.6 m/s	0.2...75 m³/h
Process connection	threaded connection R 1/2 DN15		
Application			
Application	for industrial applications		
Media	compressed air		
Note on media	air quality ISO 8573-1		
	class 141		
	class 344		
Medium temperature [°C]	0...60		
Pressure rating [bar]	16		
Pressure rating [MPa]	1.6		
MAWP (for applications according to CRN) [bar]	16		
Electrical data			
Operating voltage [V]	18...30 DC; (to SELV/PELV)		
Current consumption [mA]	< 110		
Protection class	III		

SD6000

Compressed air meter

SDR12DGXFPKG/US-100

Reverse polarity protection		yes		
Power-on delay time	[s]	1		
Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1		
Outputs				
Total number of outputs		2		
Output signal		switching signal; analogue signal; pulse signal; IO-Link; (configurable)		
Electrical design		PNP		
Number of digital outputs		2		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	250; (per output)		
Number of analogue outputs		1		
Analogue current output	[mA]	4...20; (scalable)		
Max. load	[Ω]	500		
Pulse output		consumed quantity meter		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Measuring/setting range				
Measuring range		10...1250 l/min	0.3...103.6 m/s	0.2...75 m³/h
Display range		0...1500 l/min	0...124.3 m/s	0...90 m³/h
Set point SP		10...1250 l/min	0.8...103.6 m/s	0.6...75 m³/h
Reset point rP		4...1244 l/min	0.3...103.1 m/s	0.2...74.6 m³/h
Analogue start point ASP		0...938 l/min	0...77.7 m/s	0...56.3 m³/h
Analogue end point AEP		312...1250 l/min	25.9...103.6 m/s	18.7...75 m³/h
In steps of		1 l/min	0.1 m/s	0.1 m³/h
Volumetric flow quantity monitoring				
Pulse value		0.001...1000000 m³		
In steps of		0.001 m³		
Pulse length	[s]	0,02...2		
Temperature monitoring				
Measuring range	[°C]	0...60		
Display range	[°C]	-12...72		
Accuracy / deviations				
Flow monitoring				
Repeatability	[% of the measured value]	± 1,5		
Accuracy (in the measuring range)		± (3 % MW + 0,3 % MEW) / ± (6 % MW + 0,6 % MEW); (class 141 /; class 344; conditions: installation to DIN ISO 2533; installation in pipes: DN15)		

SD6000

Compressed air meter

SDR12DGXFPKG/US-100

Temperature monitoring			
Accuracy	[K]	± 2; (medium flow in the limit area of the flow measurement range)	
Response times			
Flow monitoring			
Response time	[s]	0.1; (dAP = 0)	
Damping process value dAP in steps	[s]	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1	
Software / programming			
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9 CDV	
Profiles		no profile	
SIO mode		yes	
Required master port type		A	
Process data analogue		3	
Process data binary		2	
Min. process cycle time	[ms]	4.1	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	262
Operating conditions			
Ambient temperature	[°C]	0...60	
Storage temperature	[°C]	-20...85	
Max. relative air humidity	[%]	90	
Protection		IP 65	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
CPA approval		model number	002TG
		accuracy class	-
		maximum allowable error	± 4 % FS
		Q (min)	0,2 m³/h
		Q (t)	-
		Q (max)	75 m³/h
Vibration resistance		DIN EN 68000-2-6	5 g (55...2000 Hz)
MTTF	[years]	227	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	942.5	
Materials		PBT-GF20; NBR; PC; stainless steel (1.4301 / 304); PTFE; brass coated; FKM; aluminium powder-coated	

SD6000

Compressed air meter

SDR12DGXFPKG/US-100

Materials (wetted parts)		stainless steel (1.4301 / 304); FKM; ceramics glass passivated; PEEK GF30; polyester; aluminium
Tightening torque	[Nm]	50
Process connection		threaded connection R 1/2 DN15

Displays / operating elements


Display	Display unit	5 x LED, green (Nl/min, Nm³/h, Nm/s, Nm³, °C)
	function display	1 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit

Remarks


Remarks	MW = measured value
	MEW = Final value of the measuring range
	Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533.
	For information about installation and operation please see the operating instructions.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT1/IO-Link: switching output volumetric flow quantity monitoring
Pulse output quantity meter
signal output Preset counter

OUT2/InD: switching output volumetric flow quantity monitoring / Temperature monitoring
analogue output volumetric flow quantity monitoring / Temperature monitoring
input counter reset