PP7021


Pressure switch with ceramic measuring cell

PP-250-SBG14-QFRKG/US/ /V

Article no longer available - archive entry

Alternative articles: PP7551 or PP0521
When selecting an alternative article and accessories please note that technical data may differ!

PP755x = DC pnp, PP052x = DC npn



Product characteristics			
Number of inputs and outputs	Number of digital outputs: 2		
Measuring range	0...250 bar	0...3630 psi	0...25 MPa
Process connection	threaded connection G 1/4 external thread internal thread:M5		
Application			
Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.		
Medium temperature [°C]	-25...80		
Min. bursting pressure	850 bar	12300 psi	85 MPa
Pressure rating	400 bar	5800 psi	40 Mpa
Type of pressure	relative pressure		
Electrical data			
Operating voltage [V]	9.6...30 DC; (PP2000 with sensor: > 18)		
Current consumption [mA]	< 45		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		

PP7021

Pressure switch with ceramic measuring cell

PP-250-SBG14-QFRKG/US/ /V

Power-on delay time [s]	0.3		
Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 2		
Outputs			
Total number of outputs	2		
Output signal	switching signal		
Electrical design	PNP/NPN		
Number of digital outputs	2		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2		
Permanent current rating of switching output DC [mA]	250		
Switching frequency DC [Hz]	< 170		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	0...250 bar	0...3630 psi	0...25 MPa
Set point SP	3...250 bar	40...3630 psi	0.3...25 MPa
Reset point rP	2...249 bar	20...3610 psi	0.2...24.9 MPa
In steps of	1 bar	10 psi	0.1 MPa
Accuracy / deviations			
Switch point accuracy [% of the span]	< ± 1,5		
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Linearity deviation [% of the span]	< ± 0,5		
Hysteresis deviation [% of the span]	< ± 0,1		
Long-term stability [% of the span]	< ± 0,1; (per year)		
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,2; (-25...80 °C)		
Temperature coefficient span [% of the span / 10 K]	< ± 0,3; (-25...80 °C)		
Response times			
Response time [ms]	< 3		
Damping process value dAP [s]	0...4		
Software / programming			
Adjustment of the switch point	programming unit / teach function		

PP7021

Pressure switch with ceramic measuring cell

PP-250-SBG14-QFRKG/US/ /V

Interfaces			
Communication interface		EPS	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data			
Materials		stainless steel (1.4301 / 304); PA	
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles		100 million	
Process connection		threaded connection G 1/4 external thread internal thread:M5	
Restrictor element integrated		no (can be retrofitted)	
Displays / operating elements			
Display		operation	LED, green
		switching status	2 x LED, yellow
Teach function		yes	
Remarks			
Pack quantity		1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



PP7021

Pressure switch with ceramic measuring cell

PP-250-SBG14-QFRKG/US/ /V

Connection

