

SCR12ABAFPKG/PH



Technical drawing of the LED module showing side and front views with dimensions.

Side View Dimensions:

- Total length: 83
- Distance from mounting base to LED module: 13,2
- Distance from mounting base to potentiometer: 35
- Distance from potentiometer to LED module: 23,5
- Distance from potentiometer to LED module (inner): 12
- Mounting base diameter: $\varnothing 9$
- LED module diameter: $\varnothing 7,7$
- Mounting base thread: $G1\frac{1}{2}$
- LED module thread: $\varnothing 27$
- Mounting base height: 60

Front View Dimensions:

- Width: 41
- Height: 41
- LED module label: LED
- Potentiometer label: POTI



輸入和輸出總數	數字輸出數量: 1
製程連接	G 1/2 外螺紋

抗壓强度	[bar]	30
------	-------	----

工作電壓	[V]	20...36 DC
電流損耗	[mA]	< 45
反相保護		是
開機延遲時間	[s]	< 20

輸入和輸出總數	數字輸出數量: 1
---------	-----------

輸出數量	1
輸出信號	開關信號
電氣設計	PNP
數字輸出數量	1
輸出功能	常開/常閉；（可設定參數）
開關輸出DC電壓降最大值 [V]	2.5
開關輸出DC的持續電流負載 [mA]	400
短路保護	是
短路保護類型	脈衝

ST0518



流量監控器

SCR12ABAFPKG/PH

過載保護		是	
測量/設定範圍			
氣體介質			
設定範圍		[cm/s]	150...300
精度/偏差			
介質溫度梯度最大值		[K/min]	15
反應時間			
反應時間		[s]	1...10
氣體介質			
反應時間		[s]	1...10
軟體/編程			
開關點調整		電位計	
工作條件			
環境溫度		[°C]	-20...80
外殼防護等級		IP 67	
機械技術數據			
材質		PBT-GF20	
材質(潮濕部件)		不鏽鋼(1.4305/303)	
製程連接		G 1/2 外螺紋	
顯示器/操作件			
顯示		功能	11 x LED
附件			
供貨範圍		密封圈： 2 x AMF 30	
		螺絲刀	
注釋			
包裝單位		1 件數	

ST0518

流量監控器



SCR12ABAFPKG/PH



電氣連接

電纜: 2 m, PUR; 3 x 0.5 mm², PVC

連接



BN = 棕色
BU = 藍色
BK = 黑色