

E20217




Fibre optic through beam sensor

FE-30-P-A-M6/2M

Article no longer available - archive entry

Alternative article: E20328 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



Application

Function principle Through-beam sensor

Detection zone

Range with fibre optic amplifier type OIF

OIF

Range of fibre optics [mm] 270

Operating conditions

Ambient temperature [°C] -20...80

E20217



Fibre optic through beam sensor

FE-30-P-A-M6/2M

Mechanical data	
Version of sensing head	straight
Sensing head thread	M6
Sensing head length [mm]	35
Total length [mm]	2000
Min. bending radius [mm]	30
Fibre arrangement	●
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	PVC
Remarks	
Pack quantity	1 pcs.

Article no longer available - archive entry

Alternative article: E20328 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!