


IE5243



Inductive sensor

IEA3002,5BPOG

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Reverse polarity protection		no
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	300
Short-circuit protection		no
Overload protection		no
Detection zone		
Sensing range	[mm]	2.5
Real sensing range Sr	[mm]	2.5 ± 10 %
Operating distance	[mm]	0...2.03
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...20
Operating conditions		
Ambient temperature	[°C]	-15...70
Protection		IP 65
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Materials		brass nickel-plated; sensing face: PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow


IE5243



Inductive sensor

IEA3002,5BPOG

Accessories	
Accessories (supplied)	lock nuts: 2
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 2 m, PVC; 3 x 0.14 mm ²	
Connection	



Core colours :

BN = brown
BU = blue
BK = black

Article no longer available - archive entry