




## AS-Interface control cabinet module

CabinetModule 4DI 4DO R C

Article no longer available - archive entry



### Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 280
Max. current load total	[A]	6

### Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of relay outputs: 4
------------------------------	---

### Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply	[V] 18...30
Max. total current rating of inputs	[mA] 200
Input current High	[mA] > 3
Input current Low	[mA] < 1.5
Min. switching level high signal	[V] 10
Digital inputs protected against short circuits	yes

# AC2808



## AS-Interface control cabinet module

CabinetModule 4DI 4DO R C

Outputs		
Electrical design		AS-i
Voltage range DC [V]		24
Voltage range AC [V]		240
Max. current load per output [mA]		2500
Number of relay outputs		4
Electrically separated		yes
Operating conditions		
Ambient temperature [°C]		-25...50
Protection		IP 20
Tests / approvals		
EMC	EN 50295	
	EN 50178	
AS-i classification		
AS-i profile		S-7.0
AS-i I/O configuration [hex]		7
AS-i ID code [hex]		0
AS-i certificate		11601
Mechanical data		
Type of mounting	mounting on DIN rail and panel; string mounting possible	
Materials	PA; PVC	
Displays / operating elements		
Display	switching status	LED, yellow
	operation	LED, green
Remarks		
Remarks	Do not connect any of the following points to an external potential: I-, I+, I1, I2, I3, I4	
	The connections are electrically connected with the AS-i cable.	
Pack quantity	1 pcs.	




## AS-Interface control cabinet module

CabinetModule 4DI 4DO R C

### Electrical connection

COMBICON:

### Connection



A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
O4-O3/O2/O1	external supply + (DC) / L1 (AC)
N	external supply - (DC) / N (AC)
I1...I4	switching input sensor 1...4
O1...O4	switching output actuator 1...4

Article no longer available - archive entry