




Continuous level sensor (guided wave radar)

LR0000--BR34AQPKG/US

For high process temperatures: The temperature at the process connection is decisive. The actual medium temperature may be higher.



- | | |
|---------|-----------------|
| 1 | Sealing |
| A | active range |
| I1 / I2 | inactive ranges |



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Probe length L [mm]	100...2000
Process connection	threaded connection G 3/4 external thread

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	Liquids
Dielectric constant of the medium	≥ 1,8; (for media with a dielectric constant of 1.8...5 (e.g. oils), a coaxial pipe is needed for operation)
Recommended media	water; hydrous media; oils; oil-based media
Process temperature [°C]	-25...80; (90 < 1 h ; see note under remarks)
Pressure rating [bar]	16
Vacuum resistance [mbar]	-1000

Electrical data

Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 25



Continuous level sensor (guided wave radar)

LR0000--BR34AQPKG/US

Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 3
Measuring principle	guided wave radar
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2
Outputs	
Total number of outputs	2
Output signal	switching signal; IO-Link
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes
Measuring/setting range	
Probe length L [mm]	100...2000
Active range A [mm]	L-40; (when set to oil and oil based media: L-60)
Inactive range I1 / I2 [mm]	30 / 10; (when set to oil and oil based media: 30 / 30)
Sampling rate [Hz]	4
Setting range	
Set point SP [mm]	15...L-30
Note on setpoint SP	when set to oil and oil based media: 35...L-30
Reset point rP [mm]	10... L-35
Note on reset point rP	when set to oil and oil based media: 30...L-35
In steps of [mm]	5
Hysteresis [mm]	> 5
Accuracy / deviations	
Repeatability [mm]	± 5
Measuring error [mm]	± 7
Offset error [mm]	5
Resolution [mm]	1
Temperature drift per 10 K	± 0.2 %
Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis



Continuous level sensor (guided wave radar)

LR0000--BR34AQPKG/US

SIO mode	yes				
Required master port type	A				
Process data analogue	3				
Process data binary	2				
Min. process cycle time [ms]	3.2				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>907</td></tr> </table>	Type of operation	DeviceID	default	907
Type of operation	DeviceID				
default	907				

Operating conditions

Ambient temperature [°C]	-25...60
Storage temperature [°C]	-40...85
Protection	IP 68; IP 69K; (7 days / 1 m water depth / 0.1 bar: IP 68)

Tests / approvals

EMC	<table> <tr> <td>DIN EN 61000-6-2</td><td></td></tr> <tr> <td>DIN EN 61000-6-3</td><td>: in a closed metal tank</td></tr> <tr> <td>DIN EN 61000-6-4</td><td>: in plastic or open metal tanks</td></tr> </table>	DIN EN 61000-6-2		DIN EN 61000-6-3	: in a closed metal tank	DIN EN 61000-6-4	: in plastic or open metal tanks
DIN EN 61000-6-2							
DIN EN 61000-6-3	: in a closed metal tank						
DIN EN 61000-6-4	: in plastic or open metal tanks						
Shock resistance	DIN EN 60068-2-27 50 g (11 ms) / 25 g (6 ms) with reference rod 0.5 m						
Vibration resistance	DIN EN 60068-2-6 5 g (10...2000 Hz) / 1 g (5...200 Hz) with reference rod 0.5 m						
MTTF [years]	286						
UL approval	<table> <tr> <td>UL Approval no.</td><td>H010</td></tr> <tr> <td>File number UL</td><td>E174191</td></tr> </table>	UL Approval no.	H010	File number UL	E174191		
UL Approval no.	H010						
File number UL	E174191						

Mechanical data

Weight [g]	484.4
Materials	stainless steel (304/1.4301); stainless steel (316L/1.4404); FKM; PEI
Materials (wetted parts)	stainless steel (303/1.4305); probe connection: stainless steel (316L/1.4435); PTFE; FKM; Sealing: NBR reinforced fibre
Process connection	threaded connection G 3/4 external thread

Remarks

Notes	For high process temperatures: The temperature at the process connection is decisive. The actual medium temperature may be higher.
Pack quantity	1 pcs.

Electrical connection - plug


Connector: 1 x M12; coding: A; Contacts: gold-plated



Continuous level sensor (guided wave radar)

LR0000--BR34AQPKG/US

Connection



OUT1: switching output or IO-Link
OUT2: switching output
colours to DIN EN 60947-5-2

Core colours :

BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs

Measurement deviation D at the limits of the active rod range

