
O1D106

Photoelectric distance sensor

O1DLF3KG



1 alphanumeric display 4-digit
2 programming buttons

Product characteristics		
Laser protection class		2
Housing		rectangular
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 150
Protection class		III
Reverse polarity protection		yes
Typ. lifetime	[h]	50000
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / normally closed; (programmable)
Max. current load per output	[mA]	200
Number of analogue outputs		1
Analogue current output	[mA]	4...20; (scalable IEC 61131-2)

O1D106

Photoelectric distance sensor

O1DLF3KG

Max. load	[Ω]	250	
Analogue voltage output	[V]	0...10; (scalable IEC 61131-2)	
Min. load resistance	[Ω]	5000	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Max. light spot width	[mm]	150	
Max. light spot height	[mm]	150	
Light spot dimensions refer to		75 m	
Background suppression	[m]	75...150	
Measuring/setting range			
Measuring range	[m]	1...75; (Reflector E21159)	
Sampling rate	[Hz]	1...33	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Sensor Identification; Binary Data Channel; Process Value; Sensor Diagnosis	
SIO mode		yes	
Required master port type		A	
Process data analogue		1	
Process data binary		2	
Min. process cycle time	[ms]	6	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	810
Operating conditions			
Ambient temperature	[°C]	-10...60	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
Laser protection class		2	

O1D106

Photoelectric distance sensor

O1DLF3KG

Notes on laser protection		Caution:	laser light
		Power:	<= 4,0 mW
		Wave length:	650 nm
		pulse:	1,3 ns
		Do not stare into beam.	
		Avoid exposure to the laser light.	
		laser class:	2
			EN / IEC60825-1:2007
			EN / IEC60825-1:2014
			Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[years]	106	

Mechanical data

Weight	[g]	312
Housing		rectangular
Dimensions	[mm]	59 x 42 x 52
Materials		housing: diecast zinc; front pane: glass; LED window: PC
Lens alignment		side lens

Displays / operating elements


Display	switching status	2 x LED, yellow
	operation	LED, green
	distance value, programming	alphanumeric display, 4-digit

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A




O1D106

Photoelectric distance sensor

O1DLF3KG

Connection



2: switching output or analogue output 4...20 mA / 0...10 V
4: switching output or IO-Link
5: IN1 Laser On/ Off

Other data

Parameter	Setting range	Factory setting
Uni	m, feet	m
OU1	Hno, Hnc, Fno, Fnc	Hno
SP1	1.00...75.00	10.00
nSP1	1.00...75.00	8.00
FSP1	1.00...75.00	12.00
OU2	Hno, Hnc, Fno, Fnc, I, U	I
SP2	1.00...75.00	20.00
nSP2	1.00...75.00	18.00
FSP2	1.00...75.00	22.00
ASP	0...75.00	0
AEP	0...75.00	75.00
rATE [Hz]	1...33	15
dS1	0...0.1...5	0
dr1	0...0.1...5	0
dS2	0...0.1...5	0
dr2	0...0.1...5	0
dFo	0...0.1...5	0.2
dIS	d1...3; rd1...3; OFF	d3

O1D106

Photoelectric distance sensor

O1DLF3KG

repeatability/accuracy

	repeatability of the measured values	accuracy
1...25 m	± 15 mm	± 35 mm
30 m	± 15 mm	± 35 mm
40 m	± 15 mm	± 35 mm
50 m	± 19 mm	± 39 mm
60 m	± 27 mm	± 47 mm
70 m	± 43 mm	± 63 mm

Sampling rate	
Reflector	33 Hz

repeatability/accuracy

	repeatability of the measured values	accuracy
1...75 m	± 15 mm	± 35 mm

Sampling rate	
Reflector	1 Hz
The values apply at	
Extraneous light on the object	< 100 klx
constant ambient conditions	23 °C / 960 hPa
minimum power-on time in minutes	10