

VDOAH050MSS0007H05STGH050MSS

Technical drawing of a 1/2 inch NPT x 1/2 inch NPT elbow fitting. The drawing shows two views: a side view and an end view. The side view shows a straight fitting with a length of 49.5 mm and a thread length of 15.5 mm. The end view shows an elbow fitting with a height of 26.5 mm and a base diameter of 36.5 mm. Both fittings have an M12x1 thread and a 14 mm hexagonal base.



Posebno svojstvo	bez silikona; bez halogena; Pozlaćeni kontakti; Primjeren za povlačni lanac
Bez silikona	da

Radni napon	[M]	< 60 AC/DC
Zaštitna klasa		II
Maks. ukupno strujno opterećenje	[A]	4
Sveukupna strujna opteretivost (UL)	[A]	3

Temperatura okoline	[°C]	-25...90
Napomena o temperaturi okoline		cULus: ...75
Temperatura okoline (pokretna)	[°C]	-25...90
Napomena o temperaturi okoline (pokretna)		cULus: ...75
Temperatura skladištenja	[°C]	-25...55
Skladišna vlažnost	[%]	10...100
Drugi klimatski uvjeti za pohranu u skladu s navedenim razredom		1K22/ DIN 60721-3-1
Zaštita		IP 65; IP 67; IP 68; IP 69K

Spojni kabel

VDOAH050MSS0007H05STGH050MSS

Mehanički podaci


Težina	[g]	277
Materijal ulivenog tijela		TPU
Zaporna matica materijala		Mjed, niklovano
Materijal za brtvljenje		FKM
Primjeren za povlačni lanac		da
Primjeren za povlačni lanac	Za elastično giblјvost	min. promjer kabela 10 x
	Brzina postupta	max 3,3 m/s pri 5 m horizontalne dolzine i max. pospesak od 5m/s
	Ciklus gibajna	> 5 Mio.
	Torzijska trdoca	± 180 °/m

Opaske

Upute	Pogledajte tehničku napomenu pod „Preuzimanja”
Količina pakiranja	1 kom.

Električni priključak - utikač


Poveznik: 1 x M12, ravno; kodiranje: A; Oblikovana karoserija: TPU; Zaključavanje: Mjed, niklovano; Kontakti: pozlaćeno; Zakretni moment pritezanja: 0,6...1,5 Nm



Električni priključak

Kabel: 7 m, PUR, bez halogena, crno, Ø 4,6 mm; 5 x 0,34 mm² (42 x Ø 0,1 mm)

Priključak



Spojni kabel

VDOAH050MSS0007H05STGH050MSS

Električni priključak - utičnica

Poveznik: 1 x M12, kutno; kodiranje: A; Oblikovana karoserija: TPU; Zaključavanje: Mjed, niklovano; Brtva: FKM; Kontakti: pozlaćeno; Zakretni moment pritezanja: 0,6...1,5 Nm



dijagrami i grafikoni

Smanjivanje snage $I_{max} * 0.8$ DIN EN 60512-5-2

X Temperatura okoline [°C]

Y Struja [A]