


AC1404



AS-Interface PROFINET gateway with PLC

SmartPLC DataLine 2ASi PN



Electrical data		
Operating voltage	[V]	18...32 DC; (AUX; AS-i: 21...31,6 V DC)
Current consumption	[mA]	< 500; (AUX / AS-i 1)
Max. current consumption from AS-i	[mA]	500; (with external supply: 10 mA; AS-i 2: 10 mA)
Number of AS-i masters		2
Electrical separation		yes
Outputs		
Voltage range DC	[V]	to PELV
Interfaces		
Communication interface		Ethernet; OPC-UA
Ethernet - EtherCAT		
Protocol		EtherCAT
Usage type		programming
Ethernet - EtherNet/IP		
Protocol		EtherNet/IP
Usage type		programming
Ethernet - Modbus TCP		
Transmission rate		10 MBaud; 100 MBaud
Connector type		RJ45
Protocol		Modbus TCP



AS-Interface PROFINET gateway with PLC

SmartPLC DataLine 2ASi PN

Usage type	programming	
Ethernet - PROFINET		
Transmission rate	100 MBaud	
Connector type	RJ45	
Protocol	PROFINET	
Usage type	data transmission	
Note on interfaces	Device Class B	
Ethernet - TCP/IP		
Transmission rate	10 MBaud; 100 MBaud	
Connector type	RJ45	
Protocol	TCP/IP	
Usage type	programming	
Ethernet - UDP/IP		
Transmission rate	10 MBaud; 100 MBaud	
Connector type	RJ45	
Protocol	UDP/IP	
Usage type	programming	
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection	IP 20	
Tests / approvals		
MTTF	[years]	37
AS-i classification		
AS-i version	3.0	
AS-i master profile	M4	
AS-i certificate	97301	
Mechanical data		
Weight	[g]	726
Housing	housing for DIN rail mounting	
Materials	aluminium powder-coated; steel sheet galvanised; PC	
Displays / operating elements		
Display	function	1 x LED, red/green
		full graphic LCD display
Accessories		
Items supplied	terminals	
Remarks		
Pack quantity	1 pcs.	



AS-Interface PROFINET gateway with PLC

SmartPLC DataLine 2ASi PN

Electrical connection

terminals: ...2.5 mm²

Connection

	AS-i 2+
	AS-i 2-
	AS-i 1+
	AS-i 1-
	FE
	n.c.
	24 V
	0 V