


Flow sensor for connection to an evaluation unit

STM12ABBE1 6m

Article no longer available - archive entry



Product characteristics

Process connection	M12 x 1
--------------------	---------

Application

Application	Ex zone 1
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Liquids

Application	Ex zone 1
Medium temperature [°C]	-25...80

Gases

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Connection to control monitor	VS 0100 Ex
-------------------------------	------------

Measuring/setting range

Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Gases

Setting range [cm/s]	5...1500
----------------------	----------

Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

Response times

Response time [s]	1...10
-------------------	--------

Liquids

Response time [s]	1...10
-------------------	--------

Gases

Response time [s]	1...10
-------------------	--------

Operating conditions

Protection	IP 67
------------	-------

Mechanical data

Housing	threaded type
---------	---------------

ST1211



Flow sensor for connection to an evaluation unit

STM12ABBE1 6m

Dimensions	[mm]	M12 x 1 / L = 43
Thread designation		M12 x 1
Materials		stainless steel (316Ti/1.4571)
Process connection		M12 x 1


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m; 4 x 0.25 mm²

Connection



	Core colours :
BN =	brown
GN =	green
WH =	white
YE =	yellow