




Capacitive sensor

KB-3020-APKG/NI/10M/PH

Article no longer available - archive entry

Discontinuation date: 31.03.2017



Product characteristics

Electrical design		PNP
Output function		normally closed
Sensing range	[mm]	3...20
Housing		cylindrical
Dimensions	[mm]	Ø 34 / L = 81

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	13; (24 V)
Protection class		II
Reverse polarity protection		yes

Outputs

Electrical design		PNP
Output function		normally closed
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	40
Short-circuit proof		yes
Overload protection		yes

Detection zone

Sensing range	[mm]	3...20
Sensing range adjustable		yes
Factory setting sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2

KB5082



Capacitive sensor

KB-3020-APKG/NI/10M/PH

Accuracy / deviations		
Correction factor		glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-15...15
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes; (increased immunity to conducted radio frequency interference)
Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	778
Mechanical data		
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34 / L = 81
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		Mounting clamps: 1 screwdriver: 1
Remarks		
Pack quantity		1 pcs.

KB5082




Capacitive sensor

KB-3020-APKG/NI/10M/PH

Electrical connection

Cable: 10 m, PUR; 3 x 0.5 mm²

Connection



Core colours :

BN = brown
BU = blue
BK = black

Article no longer available - archive entry

Discontinuation date: 31.03.2017