


E10868



Spojni kabel s utičnicom

ADOGH030MSS0005E03



Električni podaci

Radni napon	[V]	< 250 AC / < 300 DC
-------------	-----	---------------------

Radni uvjeti

Temperatura okoline	[°C]	-25...90
Zaštita		IP 67

Mehanički podaci

Težina	[g]	198,3
Dimenzije	[mm]	15 x 15 x 43
Materijali		TPU
Materijal ulivenog tijela		TPU
Zaporna matica materijala		Mjed, niklovano

Opaske

Količina pakiranja		1 kom.
--------------------	--	--------

E10868



Spojni kabel s utičnicom


ADOGH030MSS0005E03

Električni priključak


Kabel: 5 m, PVC, Narančasto, Ø 5 mm; 3 x 0,34 mm² (19 x Ø 0,16 mm) / AWG 22

Električni priključak - utičnica

Poveznik: 1 x M12, ravno; kodiranje: C; Oblikovana karoserija: TPU; Zaključavanje: Mjed, niklovano; Zakretni moment pritezanja: 0,5 Nm



Priključak



BK =	Boje žica :
BU =	crno
GN/YE =	Plavo
	zeleno/žuto