E20532


Fibre optic through-beam sensor

FE-00-M-V-M4/1m

Article no longer available - archive entry

Alternative articles: E20533

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Through-beam sensor
Detection zone		
Range with fibre-optic amplifier type		OKF; OUF
OKF		
Range of fibre optics	[mm]	120
OUF		
Range of fibre optics	[mm]	120
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Version of sensing head		straight
Sensing head thread		M4
Sensing head length	[mm]	15
Total length	[mm]	1000

E20532

Fibre optic through-beam sensor

FE-00-M-V-M4/1m

Min. bending radius	[mm]	20
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		metal silicone
Remarks		
Pack quantity		1 pcs.