
SA4114

Flow sensor

SAEXXXXB50KG/US-100



L 100 mm
1 LEDs Display unit
I, II not used
2 alphanumeric display 4-digit red/green
3 programming buttons
4 upper part of the housing can be rotated 345°

Product characteristics		
Number of inputs and outputs		Number of analogue outputs: 2
Process connection		diameter Ø 8 mm
Application		
Special feature		Gold-plated contacts
Media		water; glycol solutions; air; oils
Note on media		low-viscosity oils with viscosity: ≤ 40 mm²/s (104 °F)
		high-viscosity oils with viscosity: > 40 mm²/s (104 °F)
Medium temperature	[°F]	-4...212
Pressure rating	[bar]	50
Electrical data		
Operating voltage	[V]	18...30 DC

SA4114

Flow sensor

SAEXXXXB50KG/US-100

Current consumption	[mA]	< 100
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	10
Inputs / outputs		
Number of inputs and outputs		Number of analogue outputs: 2
Outputs		
Total number of outputs		2
Output signal		analogue signal
Number of analogue outputs		2
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	350
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	100
Operating mode		relative; absolutely liquid; absolutely gaseous; (absolute: reference measurement recommended; Factory setting: relative)
Liquids		
Resolution	[ft/s]	0.05
Analogue start point ASP	[ft/s]	0...7.95
Analogue end point AEP	[ft/s]	1.9...9.85
Gases		
Resolution	[ft/s]	2
Analogue start point ASP	[ft/s]	0...264
Analogue end point AEP	[ft/s]	64...328
Temperature monitoring		
Measuring range	[°F]	-4...212
Resolution	[°F]	0.5
Analogue start point	[°F]	-4...169
Analogue end point	[°F]	39...212
In steps of	[°F]	0.5
Liquid media - absolute operating mode		
Setting range	[ft/s]	0...9.85
Greatest sensitivity	[ft/s]	0.15...9.85
Liquid media - relative operating mode		
Setting range	[ft/s]	0...19.5
Greatest sensitivity	[ft/s]	0.15...9.85
Gases - operating mode "absolute"		
Setting range	[ft/s]	0...328
Greatest sensitivity	[ft/s]	6...328

SA4114

Flow sensor

SAEXXXXB50KG/US-100

Gases - operating mode "relative"			
Setting range	[ft/s]	0...656	
Greatest sensitivity	[ft/s]	6...328	
Accuracy / deviations			
Temperature drift	[cm/s x 1/K]	0,01 fps x 1/K (< 68 °F; > 158 °F)	
Temperature gradient	[K/min]	100	
Absolute operating mode			
Repeatability		0,05 m/s; (water; flow velocity: 0,05...3 m/s)	
Relative operating mode			
Accuracy		± (7 % MW + 2 % MEW); (for relative mode in the range of maximum sensitivity under the following conditions:; water: 68...158 °F; inlet length: 5 ft; DN25 (DIN 2448); mounting position according to instructions; Accuracy can differ for other media and mounting positions.)	
Repeatability		0,05 m/s; (water; flow velocity: 0,05...3 m/s)	
Temperature monitoring			
Temperature drift		± 0,003 K/°F	
Accuracy	[K]	± 0,3 / ± 1; (water; flow velocity: 1...9,85 fps / air; flow velocity: > 32,8 fps)	
Response times			
Response time	[s]	0.5; (T09; water; glycol: 0,8 s; air: 7 s; oil: 1,8 s; each T09)	
Temperature monitoring			
Dynamic response T05 / T09	[s]	1,5 (T09); (water; flow velocity: 1...9,85 fps)	
Software / programming			
Parameter setting options		medium selection; Damping; Teach function; display can be rotated and switched off; standard unit of measurement; process value colour	
Operating conditions			
Ambient temperature	[°F]	-40...176	
Storage temperature	[°F]	-40...212	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		DIN EN 60947-5-9	
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	179	
UL approval		UL Approval no.	I018
		File number UL	E174189
Mechanical data			
Weight	[g]	262	
Materials		stainless steel (1.4404 / 316L); PBT-GF20; PBT-GF30	
Materials (wetted parts)		stainless steel (1.4404 / 316L)	
Process connection		diameter Ø 8 mm	
Displays / operating elements			
Display		Display unit	6 x LED, green (%, fps, gpm, cfm, °F, 10^3)
		measured values	alphanumeric display, red/green 4-digit

SA4114

Flow sensor

SAEXXXXB50KG/US-100


Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



	colours to DIN EN 60947-5-2
OUT1:	analogue output Temperature monitoring
OUT2:	analogue output volumetric flow quantity monitoring
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white