




Set otomatisasi AS-Interface untuk aktuatur katup pneumatik

Added Value package AS-i T5



Karakteristik produk

Fungsi output		PNP
Jangkauan pendeteksian [mm]		4

Data kelistrikan

Konsumsi arus maks. dari AS-i [mA]		160
Tegangan pengoperasian AUX DC [V]		26.5...31.6; ("kelas suplai 2" menurut cULus)

Input/output

Jumlah input dan output		Jumlah input digital: 2; Jumlah output digital: 1
-------------------------	--	---

Input

Jumlah input digital		2
----------------------	--	---

Output

Jumlah output digital		1
Fungsi output		PNP

Zona pendeteksian

Jangkauan pendeteksian [mm]		4
-----------------------------	--	---

Klasifikasi AS-i

Versi AS-i		2.1
Profil AS-i		S-7.A.E



Set otomatisasi AS-Interface untuk aktuatur katup pneumatik

Added Value package AS-i T5

Konfigurasi I/O AS-i	[hex]	7
Kode ID AS-i	[hex]	A.E

Data teknis		
Berat	[g]	900.95
Pemasangan		non-flush mountable
Jarak lubang	[mm]	130
Tinggi poros untuk penggerak katup	[mm]	30

Aksesori	
Item dikirim	sensor ganda untuk umpan balik aktuator: 1, AC2316
	Keping target: 1, E17328
	katup solenoid: 1, Bürkert 428623
	peredam suara: 2, 780780N
	Konektor perpindahan isolasi kabel pipih: 1, E75471
	Kabel koneksi: 1, E10845

Keterangan	
Jumlah paket	1 buah

Koneksi listrik

Koneksi listrik - colokan




Koneksi

Koneksi

1	AS-i +
3	AS-i -

Koneksi listrik - soket



Output

3	tegangan eksternal -
4	output peralihan 1 +