




Gateway Modbus/TCP AS-Interface dengan PLC

ControllerE 1Mstr EN RS232

Produk tidak tersedia - entri arsip



Aplikasi	
Aplikasi	pengontrol terdesentralisasi; Gateway EtherNet/IP; server web
Data kelistrikan	
Tegangan pengoperasian [V]	24 DC; ("kelas suplai 2" menurut cULus)
Konsumsi arus [mA]	< 700
Konsumsi arus maks. dari AS-i [mA]	10
Konsumsi daya maks. [VA]	10
Jumlah master AS-i	1
Interface	
Interface komunikasi	RS232; Ethernet
Ethernet	
Laju transmisi	10; 100
Protokol	Modbus TCP; TCP/IP
Tipe penggunaan	transmisi data
RS232	
Jumlah interface R232	1



Gateway Modbus/TCP AS-Interface dengan PLC

ControllerE 1Mstr EN RS232

Laju transmisi	9600...115200 Baud
Tipe konektor	RJ11
Tipe penggunaan	pemrograman
Catatan tentang interface	diisolasi secara elektrik

Kondisi pengoperasian

Suhu sekitar [°C]	0...60
Suhu penyimpanan [°C]	-20...70
Kelembapan udara relatif maks. [%]	95
Perlindungan	IP 20

Klasifikasi AS-i

Versi AS-i	2.1
Profil master AS-i	M3
Sertifikat AS-i	61109

Data teknis

Casing	casing untuk pemasangan rel DIN
Material	aluminium; pelat baja galvanis

Elemen display/pengoperasian

Display	fungsi	3 x LED, merah
		4 x LED, hijau
		2 x LED, kuning
		display LCD grafis penuh

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Koneksi

