




Gateway DeviceNet AS-Interface dengan PLC

ControllerE 2Master DN RS232

Produk tidak tersedia - entri arsip



Aplikasi	
Aplikasi	pengontrol terdesentralisasi; Gateway DeviceNet
Data kelistrikan	
Tegangan pengoperasian [V]	24 DC
Konsumsi arus [mA]	< 500
Konsumsi arus maks. dari AS-i [mA]	10
Konsumsi daya maks. [VA]	10
Jumlah master AS-i	2
Interface	
Interface komunikasi	RS232; CAN
CAN	
Protokol	DeviceNet
Tipe penggunaan	transmisi data
Catatan tentang interface	Group 2 only Slave



Gateway DeviceNet AS-Interface dengan PLC

ControllerE 2Master DN RS232

RS232	
Jumlah interface R232	1
Laju transmisi	9600...115200 Baud
Tipe konektor	RJ11
Tipe penggunaan	pemrograman
Catatan tentang interface	diisolasi secara elektrik

Kondisi pengoperasian

Suhu sekitar	[°C]	0...60
Suhu penyimpanan	[°C]	-20...70
Kelembapan udara relatif maks.	[%]	95
Perlindungan		IP 20

Klasifikasi AS-i

Versi AS-i	2.1
Profil master AS-i	M3
Sertifikat AS-i	61112

Data teknis

Berat	[g]	549.4
Casing		casing untuk pemasangan rel DIN
Material		aluminium; pelat baja galvanis

Elemen display/pengoperasian

Display	fungsi	4 x LED, merah
		3 x LED, hijau
		3 x LED, kuning
		display LCD grafis penuh

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Koneksi

