




Modul AS-Interface ClassicLine

ClassicLine90 4AO (C) M12 IP67



- 1 panel untuk pelabelan
2 pengaman adaptor inframerah



Aplikasi		
Aplikasi	Instalasi di lapangan	
Data kelistrikan		
Tegangan pengoperasian	[V]	26.5...31.6 DC
Konsumsi arus maks. dari AS-i	[mA]	157
Pelindung polaritas terbalik		ya
Suplai tegangan tambahan	[V]	24...30 DC; (AUX)
Suplai tegangan tambahan		opsi
Konsumsi arus maksimal dari suplai tambahan	[mA]	550; (AUX)
Input/output		
Jumlah input dan output	Jumlah output analog: 4	
Input		
Input analog presisi	[%]	0,5
Output		
Jumlah output analog		4; (koneksi aktuator 2 kawat)
Output arus analog	[mA]	0...20
Beban maks.	[Ω]	600
Resolusi output analog		16 (1 bit = 1 μA)
Output suplai aktuator		AS-i / AUX



Modul AS-Interface ClassicLine

ClassicLine90 4AO (C) M12 IP67

Kondisi pengoperasian		
Suhu sekitar	[°C]	0...70
Suhu penyimpanan	[°C]	-20...85
Kelembapan udara relatif maks.	[%]	90; (non kondensasi)
Ketinggian maks. di atas permukaan laut	[m]	2000
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 50295	
	EN 61000-6-4	: 2001
	EN 61000-6-2	: 2001
MTTF	[ANN]	135
Klasifikasi AS-i		
Pengalamatan AS-i	soket pengalamatan; Pengalamatan IR dimungkinkan	
AS-i master profile	M3; M4	
Profil AS-i	S-7.3.6	
Konfigurasi I/O AS-i	[hex]	7
Kode ID AS-i	[hex]	3.6
Data teknis		
Berat	[g]	224.65
Tipe pemasangan	Interface AS-i untuk bagian bawah FC/FC-E	
Material	PBT	
Torsi pengencangan	[Nm]	0.6...0.8
Elemen display/pengoperasian		
Display	sinyal analog	LED, kuning saluran AO1...AO4
	operasi	LED, hijau AS-i, AUX
	kesalahan	LED, merah
Koneksi listrik		
Koneksi modul	Kabel pipih	
Aksesori		
Aksesori (opsional)	Bagian bawah modul	
Keterangan		
Jumlah paket	1 buah	




Modul AS-Interface ClassicLine

ClassicLine90 4AO (C) M12 IP67

Koneksi listrik

Konektor: M12; pengkodean: A



1	AO+ output analog
2	n.c.
3	AO- output analog 0V
4	n.c.
5	ground fungsional