




Gateway DeviceNet AS-Interface dengan PLC

ControllerE 1Master DN RS232

Produk tidak tersedia - entri arsip



Aplikasi		
Aplikasi	pengontrol terdesentralisasi; Gateway DeviceNet	
Data kelistrikan		
Tegangan pengoperasian	[V]	24 DC
Konsumsi arus	[mA]	500
Konsumsi arus maks. dari AS-i	[mA]	10
Konsumsi daya maks.	[VA]	10
Jumlah master AS-i		1
Interface		
Interface komunikasi	RS232; CAN	
CAN		
Protokol	DeviceNet	
Tipe penggunaan	transmisi data	
Catatan tentang interface	Group 2 only Slave	



Gateway DeviceNet AS-Interface dengan PLC

ControllerE 1Master DN RS232

RS232		
Jumlah interface R232		1
Laju transmisi		9600...115200 Baud
Tipe konektor		RJ11
Tipe penggunaan		pemrograman
Catatan tentang interface		diisolasi secara elektrik

Kondisi pengoperasian

Suhu sekitar	[°C]	0...60
Suhu penyimpanan	[°C]	-20...70
Kelembapan udara relatif maks.	[%]	95
Perlindungan		IP 20

Klasifikasi AS-i

Versi AS-i		2.1
Profil master AS-i		M3
Sertifikat AS-i		61111

Data teknis

Casing		casing untuk pemasangan rel DIN
Material		aluminium; pelat baja galvanis

Elemen display/pengoperasian

Display	fungsi	3 x LED, merah
		4 x LED, hijau
		2 x LED, kuning
		display LCD grafis penuh

Keterangan

Jumlah paket		1 buah
--------------	--	--------

Koneksi listrik

Koneksi		
---------	--	--

