


DTE100



Unit evaluasi RFID LF/ HF

DTELF/HFABRWDPUS00




Aplikasi		
Aplikasi	hingga 4 kepala baca/tulis tipe ANT41x/ANT51x	
Data kelistrikan		
Tegangan pengoperasian	[V]	18...30 DC
Konsumsi arus	[mA]	< 3000
Input/output		
Jumlah input dan output	Jumlah output digital: 4	
Output		
Jumlah output digital	4	
Beban arus maks. per output	[mA]	500; (IO 1,2; IO 3,4: 1000 mA)
Interface		
Interface komunikasi	PROFIBUS DP	
Pengaturan pabrik	Alamat IP: 192.168.0.79	
	subnet maks: 255.255.255.0	
	alamat IP gateway: 192.168.0.100	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...60
Suhu penyimpanan	[°C]	-20...85
Perlindungan	IP 67	
Pengujian/persetujuan		
Tahan guncangan	IEC 60068-2-27	15 g 11 ms
Ketahanan terhadap getaran	IEC 60068-2-6	±1.6 mm (17...18 Hz) / 2 g (10...150 Hz)
MTTF	[ANN]	101.69



Unit evaluasi RFID LF/ HF

DTELF/HFABRWDPUS00

Data teknis		
Berat	[g]	390
Dimensi	[mm]	115 x 46.2 x 85
Material	bagian atas: PA Grivory GV5H oranye; bagian atas: TPE; bagian bawah: GD-AISi12	
Elemen display/pengoperasian		
Display	suplai tegangan	1 x LED, hijau
		1 x LED, kuning
	Profibus-DP	1 x LED, merah
		1 x LED, hijau
	Ethernet	1 x LED, hijau
		1 x LED, kuning
	Input/output	1 x LED, hijau
		1 x LED, kuning
Aksesori		
Item dikirim	Tutup pelindung: M12, E73004	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik - Profibus IN		
Konektor: M12; pengkodean: B		
		
1	n.c.	
2	Rx/D/TxD-N	
3	n.c.	
4	Rx/D/TxD-P	
Koneksi listrik - Profibus OUT		
Konektor: M12; pengkodean: B		
		
1	P5V	
2	RXD/TxD-N	
3	DGND	
4	RXD/TxD-P	
5	n.c.	




Unit evaluasi RFID LF/ HF

DTELF/HFABRWDPUS00

Koneksi listrik - suplai tegangan

Konektor: M12; pengkodean: A



1	24 V DC
2	n.c.
3	0 V
4	n.c.
5	n.c.