


E11596



Kabel koneksi dengan soket

ADOGH050MSA0002C02



Aplikasi		
Fitur khusus	Bebas halogen; Kontak berlapis emas; Kabel berpelindung; Kesesuaian rantai tarik	
Aplikasi	CAN bus	
Data kelistrikan		
Tegangan pengoperasian	[V]	< 30 AC / < 36 DC
Total beban arus maks.	[A]	4
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...80
Suhu penyimpanan	[°C]	-40...80
Perlindungan		IP 68
Data teknis		
Berat	[g]	163
Dimensi	[mm]	14.5 x 14.5 x 43.9
Material		PUR
Material bodi detakan		PUR
Material mur		kuningan, berlapis nikel
Kesesuaian rantai tarik		ya
Kesesuaian rantai tarik	radius pembengkokan untuk penggunaan yang fleksibel	min. 10 x diameter kabel
	radius pembengkokan untuk pemasangan tetap	min. 5 x diameter kabel
	kecepatan pergerakan	maks. 3,3 m/dtk untuk panjang pergerakan horizontal 5 m dan akselerasi maks. 5 m/dtk²
	siklus pembengkokan	> 1 Mio.



Kabel koneksi dengan soket

ADOGH050MSA0002C02

Keterangan


Jumlah paket	1 buah
--------------	--------

Koneksi listrik


Kabel: 2 m, PUR, Bebas halogen, ungu, Ø 6.8 mm, berpelindung; RD / BK: 2 x 0.25 mm² (19 x Ø 0.13 mm) + WH / BU: 2 x 0.34 mm² (19 x Ø 0.16 mm) + screen: 1 x 0.34 mm² (19 x Ø 0.16 mm)

Koneksi listrik - soket

Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: PUR; Penguncian: kuningan, berlapis nikel; Kontak: dilapisi emas



Koneksi



BK =	Warna core :
BU =	hitam
RD =	biru
WH =	merah
screen =	putih
	penutup