


DTE920



Unit evaluasi RFID UHF

DTEUHFEEABRWEIUS04

Produk tidak tersedia - entri arsip



Aplikasi

Persetujuan radio untuk Australia

Data kelistrikan

Tegangan pengoperasian [V]	24 DC
Konsumsi arus [mA]	700
Frekuensi pengoperasian [MHz]	916...927
Koneksi antena	4; (TNC Reverse)
Standar RFID	EPC Class1 GEN2/ISO 18000-6C
Daya transmisi ERP [mW]	2000
Impedansi [Ω]	50

Input/output

Jumlah input dan output Jumlah input digital: 4; Jumlah output digital: 4

Input

Jumlah input digital 4

Output

Jumlah output digital	4
Beban arus maks. per output [mA]	500

Zona pendeteksian

Ambang batas RSSI bisa disesuaikan melalui software

Software/pemrograman

Opsi pengaturan parameter Software



Unit evaluasi RFID UHF

DTEUHFEAABRWEIUS04

Interface		
Interface komunikasi		Ethernet
Ethernet		
Protokol		TCP/IP; IP
Tipe penggunaan		pengaturan parameter
Ethernet - EtherNet/IP		
Protokol		EtherNet/IP
Tipe penggunaan		transmisi data
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...55
Suhu penyimpanan	[°C]	-25...85
Perlindungan		IP 65
Data teknis		
Berat	[g]	3109
Casing		persegi panjang
Dimensi	[mm]	233.5 x 270 x 68
Material		casing: aluminium; Tutup pelindung: plastik; Soket TNC: kuningan/PTFE; konektor: kuningan/plastik
Elemen display/pengoperasian		
Display	operasi	1 x LED, merah/hijau
Keterangan		
Jumlah paket		1 buah
Koneksi listrik - Ethernet		
Konektor: 1 x M12		
		
1	TD+	
2	RD+	
3	TD-	
4	RD-	




Unit evaluasi RFID UHF

DTEUHFEAABRWEIUS04

Koneksi listrik - Koneksi proses

Konektor: 1 x M12; pengkodean: A



1	output peralihan CMN
2	input peralihan 3 / input peralihan 0
3	input peralihan CMN
4	0 V
5	U+
6	output peralihan 3 / output peralihan 1
7	output peralihan 2 / output peralihan 0
8	input peralihan 2 / input peralihan 1

Koneksi listrik - suplai arus

Konektor: 1 x M12; pengkodean: A



1	U+
2	n.c.
3	0 V
4	n.c.