




Sensor refleksi difus fiber optik

FT-30-P-A-R8



Aplikasi

Prinsip fungsi

Sensor refleksi difus

Aplikasi

Untuk digunakan di lingkungan industri

Zona pendeteksian

Jangkauan dengan tipe
amplifier fiber optik

OIF

OIF

Jangkauan fiber optik

[mm]

70

Kondisi pengoperasian

Suhu sekitar

[°C]

-20...80

Data teknis

Berat

[g]

91

Versi kepala pendeteksian

bersiku

Diameter kepala
pendeteksian

[mm]

8

Panjang total

[mm]

600

Radius pembengkokan min.

[mm]

30

Susunan fiber



Material

Adaptor: PA

Material fiber

kaca

Material kepala fiber

aluminium



Sensor refleksi difus fiber optik

FT-30-P-A-R8

Material selubung fiber	PVC
Aksesori	
Item dikirim	E20353
Keterangan	
Jumlah paket	1 buah