




Tag RFID

ID-TAG/86X54/06



Aplikasi

Suhu pengoperasian (aktif)	[°C]	-30...50
----------------------------	------	----------

Data kelistrikan

Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok	[Byte]	4
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000

Kondisi pengoperasian

Suhu sekitar	[°C]	-30...50
Perlindungan		IP 67

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	40 g 18 ms
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g 10...2000 Hz
Persetujuan radio		ISO 15693

Data teknis

Berat	[g]	57.2
Dimensi	[mm]	54 x 86 x 1
Material		PVC

Keterangan

Jumlah paket		10 buah
--------------	--	---------



Tag RFID

ID-TAG/86X54/06

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	22
ANT411 / DTI411	35
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	20
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	65
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	50
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	85
ANT513 / DTI513 / DTC510	120
ANT515 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	230